

ASTA874NN0085200A000

✓ ACTIVE

TE Internal #: ASA874N0085200A000

17 Position Circular Connector, Cable-to-Cable, Signal, Cable Mount (Free-Hanging), Electrodeposited Nickel, Zinc Alloy, PBT GF, 17 Signal Positions

[View on TE.com >](#)[Connectors > Circular Connectors > Standard Circular Connectors](#)Number of Positions: **17**Connector System: **Cable-to-Cable**Sealable: **No**Circuit Application: **Signal**Connector Mounting Type: **Cable Mount (Free-Hanging)**

Features

Electrical Characteristics

Operating Voltage	63 VDC
-------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Compatible With Approved Standards Products	UL
---	----

Dimensions

Cable Diameter Range	6 – 9.5 mm [.23 – .39 in]
----------------------	---------------------------

Body Features

Environmental Protection	IP67
--------------------------	------

Shell Plating Material	Electrodeposited Nickel
------------------------	-------------------------

Shell Base Material	Zinc Alloy
---------------------	------------

Circular Connector Insulation Material Type	PBT GF
---	--------

Mechanical Attachment

Panel Mount Feature Type	Screw Mount
--------------------------	-------------

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Operation/Application

Durability Rating	500 Cycles
Circuit Application	Signal
Shielded	Yes

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Cable-to-Cable
Sealable	No
Circular Connector Type	Plug
Shell Type	Metal

Configuration Features

Number of Positions	17
Number of Signal Positions	17

Housing Features

Circular Connector Shell Size	17
-------------------------------	----

Usage Conditions

Operating Temperature Range	-20 – 130 °C [-4 – 266 °F]
-----------------------------	----------------------------

Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Pb (3.5% in Component part) <small>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	Not Yet Reviewed for halogen content

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # AEA876F1000150A000
617 RECEPTACLE, SPEEDTEC-READY

Customers Also Bought




TE Part #T4133512041-000
M12, FRONT MOUNT, FEMALE, D, 4P,
SOLDER WIRE



TE Part #650110-000
D-436-0128



TE Part #CAT-HST-RNF3000
RNF-3000 Heat Shrink Tubing



TE Part #216026-007
55A0111-24-9



TE Part #3160193002
55A0121-24-2/6



TE Part #E0-0058-002-000
940 METAL FLANGE HINGED
COMPLETE

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_ASA874N0085200A000_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_ASA874N0085200A000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_ASA874N0085200A000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[ASA874N0085200A000](#)

English

[fuer Datenblaetter, die online konfigurierbar sind](#)

German