




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.51 – 1.03 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	FLK
Connection Capacity	Single

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple
Extraction Force	.7 – 10.2 kgf

Packaging Features

Packaging Quantity	4500
Packaging Method	Strip/Reel

Dimensions



Product Length	22.3 mm[.878 in]
Compatible Insulation Diameter Range	1.4 – 2.31 mm[.055 – .091 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	.51 – 1.03 mm²

Product Type Features

Insertion Force	Low
-----------------	-----

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Phosphor Bronze
Terminal Plating Material	Pre-Tin
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free




Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



KIT

TE Part # 7-2151161-7
[OCEAN_2.0_SPARE_PART_KIT-081F110OV](#)



TE Part # 1-444017-1
[HSG ASSY TIMER 9P](#)



TE Part # 169400
[CERTI-LOK FRAME W/O DIES](#)




TE Part # 724659-2
[EXT TOOL FOR POSITIVE .250](#)



TE Part # CAT-T4827-CH8172
[Timer Connector Housing](#)



TE Part # 2151161-2
[OCEAN_2.0_APPLICATOR-S-081F110OVA-RSA](#)



TE Part # 444017-2
[HSG ASS'Y 9 POS JR](#)




TE Part # 2305570-1
[Strip Terminal Cutter-Side Feed-No Crimp](#)

Also in the Series | Positive Lock 250



[Automotive Terminals\(1\)](#)



[Crimp Terminal Housings\(184\)](#)



[Insertion & Extraction Tools\(3\)](#)



[Insulation Boots & Sleeves\(4\)](#)



Quick Disconnects(185)

Customers Also Bought



TE Part #1326031-8
2.8MM BLD,SEAL,18AWG,REVREEL



TE Part #1743064-2
MT-2/JPT SLD 36P PLUG COVER BK




TE Part #1-1718284-2
ADAPTER 90°FOR 10-14POS. SOCKE




TE Part #185760-1
16W HYBRID RCPT HSG BLACK



TE Part #163555-8
MATE-N-LOK PIN 0,3-



TE Part #1-773119-8
EDS OVERMOLDED 2P ASSY, BLUE



TE Part #1203559-1
DUAL EXTERNAL RELAY BASE MICRO (FR)



TE Part #1952074-2
.250 SRS, RECP HSG, 2P WITH SE



TE Part #282435-2
MODULAR RELAY HOUSING



TE Part #928720-1
5P POS LOCK GEH

Documents

Product Drawings

PL 250 REC TERMINAL 20-17 AWG PTPB

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_927852-6_G.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_927852-6_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_927852-6_G.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654742_HOUSEHOLD_APPLIANCES_RAST5](#)

English

Product Specifications

[6,3mmm Positiv Lock Contact](#)

English

Application Specification

English

Application Specification

German

Application Specification

English