




MULTI-BEAM

TE Internal #: 2334530-4
PCB Mount Header, Right Angle, Board-to-Board, 31 Position, 2.54 mm / 5 mm / 5.5 mm [.1 in / .196 in / .216 in] Centerline, Fully Shrouded, Gold

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**
PCB Mount Orientation: **Right Angle**
Connector System: **Board-to-Board**
Number of Positions: **31**
Number of Rows: **4**

Features

Electrical Characteristics

Operating Voltage	200 VDC, 400 VDC, 60 VDC
-------------------	--------------------------

Dimensions

Row-to-Row Spacing	2 mm[.07 in]
Connector Width	23.62 mm[.93 in]
Connector Height	14.5 mm[.57 in]
Connector Length	63.74 mm[2.5 in]

Packaging Features

Packaging Quantity	33
Packaging Method	Tray

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Mechanical Attachment

--	--



Mating Retention	Without
Mating Alignment Type	Polarization
PCB Mount Retention Type	Hold-Down
PCB Mount Alignment Type	Hold-Down
PCB Mount Retention	With
PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Mating Alignment	With

Termination Features

Termination Post & Tail Length	2.54 mm[.1 in]
Square Termination Post & Tail Dimension	.64 mm[.025 in]
Termination Method to PCB	Through Hole - Solder

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 μm, 1.27 – 2.54 μm[50 μin][50 – 100 μin]
Contact Size	.64mm
Contact Mating Area Plating Material Thickness	.38 μm, .076 μm[15 μin][3 μin]
Mating Square Post Dimension	.64 mm[.025 in]
Contact Shape & Form	Square
PCB Contact Termination Area Plating Material Thickness	2.54 – 5.08 μm[100 – 200 μin]
Contact Layout	Matrix
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Gold
Contact Type	Blade, Tab
Contact Current Rating (Max)	100 A

Housing Features

Housing Material	High Temperature Thermoplastic Glass-Filled
Centerline (Pitch)	2.54 mm, 5.5 mm, 5 mm[.216 in][.196 in][.1 in]

Configuration Features

Number of Columns	13
-------------------	----



Number of Loaded Positions	31
Number of Signal Positions	24
Number of Power Positions	7
PCB Mount Orientation	Right Angle
Number of Positions	31
Number of Rows	4

Product Type Features

Mixed & Hybrid Header	Yes
Connector Shape	Rectangular
PCB Connector Assembly Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Fully Shrouded
Connector & Contact Terminates To	Printed Circuit Board

Body Features

Primary Product Color	Black
-----------------------	-------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2334570-4

MBPLUS,R/A,REC.,SOLDER,5LP + 24S + 2P

Customers Also Bought

TE Part #2102453-1

CeeLok FAS-T, Recpt Assy PCB, Sq, Ni

TE Part #2102453-3

CeeLok FAS-T, Recpt Assy PCB, Sq, Ni, A

TE Part #6450560-3

MBXL R/A RCPT 1P+16S+1P

TE Part #8682963001

55A0112-24-2

TE Part #1-5767007-2

MICT,260PLUG,190,ASSY,.025,REC

TE Part #1-530785-5



BOX PIN HDR ASSY 20 PS 075 CL

TE Part #2334570-4

MBPLUS,R/A,REC.,SOLDER,5LP + 24S + 2P

TE Part #5-1633860-1

CRIMPER, WIRE F



Documents

Product Drawings

MBPLUS,R/A,PLUG,SOLDER,5LP + 24S + 2P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2334530-4_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2334530-4_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2334530-4_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English