



Fiber Optics > Fiber Optic Connectors > Rugged Fiber Connectors > MC801 Fiber Connectors



Connector Shell Size: 17

Number of Positions: 8

Shell Material: Aluminum

Shell Plating Material: Nickel

EU RoHS Compliance: Compliant

Features

Other

Spring Material	Stainless Steel
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Body Features

Mating Alignment Feature Material	Stainless Steel
Shell Plating Material	Nickel

Product Type Features

Connector Shell Size	17
----------------------	----

Configuration Features

Number of Positions	8
---------------------	---

Housing Features

Shell Material	Aluminum
----------------	----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # YMC8010-F-17-08PN0  
ARINC 801, 38999 STYLE, SIZE 17-08



TE Part # YMC8017-F-17-08PN0  
ARINC 801, TYPE 1 JAM NUT CONNECTOR

Also in the Series | ARINC 801




MC801 Fiber Connectors(111)

Customers Also Bought



TE Part #1828573-1  
FOCK, TJ-SC, DUPLEX, SM



TE Part #6790994004  
HCTE-0187-0-SP



TE Part #2123524-1  
KIT, MM DUPLEX, TJ-LC, G2



TE Part #2123524-2  
KIT, SM DUPLEX, TJ-LC, G2



TE Part #6828129-1  
CO KIT, LC, MM, DUP TIGHT



TE Part #6828130-1  
CO KIT, LC, SM, DUP TIGHT



TE Part #2359410-1  
ASSEMBLY, HYBRID NanoRF/MT DC  
MODULE

Documents

Product Drawings  
ARINC 801, 38999 STYLE, SIZE 17-08  
English