

**F7533N** SUPERSEDED

Corcom | Corcom EEB

TE Internal #: 1-6609005-4

TE Internal Description: 10EBS1=F7533N S0

IEC Filtered Inlets, Corcom EEB Series

[View on TE.com >](#)

EMI &amp; EMC Solutions &gt; EMI Filters &gt; Power Entry Modules &gt; IEC Filtered Inlets, Corcom EEB Series



Filter Type: Power Line

Product Orientation: Right Angle

Leakage Current (Max) (120VAC, 60Hz): 220 µA

Leakage Current (Max) (250VAC, 50Hz): 380 µA

Current Rating: 10 A

[All IEC Filtered Inlets, Corcom EEB Series \(0\)](#)

## Features

### Mechanical Attachment

Panel Mount Feature Type	Snap-In
--------------------------	---------

### Product Type Features

Ground Choke Option	No
Filter Type	Power Line
Output Termination Type	.250" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 320/C-14

### Body Features

Product Orientation	Right Angle
---------------------	-------------

### Electrical Characteristics

Leakage Current (Max) (120VAC, 60Hz)	220 µA
Leakage Current (Max) (250VAC, 50Hz)	380 µA
Current Rating	10 A

Operating Voltage 250 VAC

### Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Also in the Series |

### Customers Also Bought



TE Part #2199230-3  
M.2 0.5PITCH 4.2H KEY B 15U" AU



TE Part #9-1393211-0  
T92S11D12-24



TE Part #8-2176070-5  
3521 33K 1% 2W

## Documents

### Product Drawings

#### 10EBS1=F7533N S0

English

---

### CAD Files

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-6609005-4\\_A1.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-6609005-4\\_A1.3d\\_stp.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-6609005-4\\_A1.2d\\_dxf.zip](#)

English

### 3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

#### 1654001\_CORCOM\_PRODUCT\_GUIDE\_EEA\_EEB

English

#### Corcom Combined Selector Charts

English