

# CA-16P1N12HZ00 - Device connector rear mounting



1619785

<https://www.phoenixcontact.com/us/products/1619785>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector rear mounting, series: CA, straight, shielded: yes, for standard and SPEEDCON interlock, No. of pos.: 16, Direction of rotation: Standard, contact connection type: Pin, Solder connection, Axial seal, Central fixing, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1243837

## Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Solder connection: proven connection technology for various litz wires
- Application-specific panel mounting optionally with thread or anti-rotation protection and lock nut

## Commercial data

Item number	1619785
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAER
GTIN	4046356821322
Weight per piece (including packing)	53.9 g
Weight per piece (excluding packing)	49.3 g
Customs tariff number	85366990
Country of origin	DE

# CA-16P1N12HZ00 - Device connector rear mounting

1619785

<https://www.phoenixcontact.com/us/products/1619785>



## Technical data

### Product properties

Product type	Circular connectors (device side)
--------------	-----------------------------------

### Connector

#### Insulating body

Coding	N
Insulation body material	PBT
Contact material	CuZn
Contact surface material	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder connection
Contact switching type	Pin
Application	Signal
Number of positions	16
Direction of rotation	Standard
Connection profile	16
Rated voltage	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Ovvoltge category	III
Degree of pollution	3
Contact diameter <b>Signal contacts</b>	1 mm
Litz wire cross-section <b>Signal contacts</b> max.	1 mm <sup>2</sup>
Nominal current per signal contact	8 A

#### Housing

Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Type of locking	for standard and SPEEDCON interlock
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

# CA-16P1N12HZ00 - Device connector rear mounting


1619785

<https://www.phoenixcontact.com/us/products/1619785>



## Drawings

Schematic diagram



Connector pin assignment


# CA-16P1N12HZ00 - Device connector rear mounting

1619785

<https://www.phoenixcontact.com/us/products/1619785>



Dimensional drawing



Installation dimensions

# CA-16P1N12HZ00 - Device connector rear mounting

1619785

<https://www.phoenixcontact.com/us/products/1619785>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1619785>

cUL Recognized	
Approval ID: E335019-20141210	
Nominal voltage $U_N$	Nominal current $I_N$
48 V	5 A
Cross section AWG	Cross section $mm^2$
18 - 18	-

UL Recognized	
Approval ID: E335019-20141210	
Nominal voltage $U_N$	Nominal current $I_N$
48 V	8 A
Cross section AWG	Cross section $mm^2$
18 - 18	-

cULus Recognized

# CA-16P1N12HZ00 - Device connector rear mounting

1619785

<https://www.phoenixcontact.com/us/products/1619785>



## Classifications

### ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

### ETIM

ETIM 9.0	EC002635
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# CA-16P1N12HZ00 - Device connector rear mounting

1619785

<https://www.phoenixcontact.com/us/products/1619785>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	173d401b-7a28-4e42-94a4-f76d17ca5322

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)