




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	25AUG2023	NK	JDB
	E1	DRAWING RE-CREATED IN CREO	23DEC2023	NK	JDB
	E2	REEL CORE DIA CHANGE	24 JUL2024	KA	LET

TAPE ON REEL PACKAGING ACCORDING TO DIN IEC 60286-3
PACKAGING UNIT: 75 PCS








CONSIDER MOUNTING POSITION; PEG RIGHT




1	-	TAPE AND REEL	6
1	-	HOOD	5
1	-	SOLDER CLIP LEFT	4
1	-	SOLDER CLIP RIGHT	3
4	-	PINS	2
1	-	HOUSING	1
474329-E	REV	DESCRIPTION	ITEM NO.
-	REV OF EACH ASSY NO. (WHEN BLANK, USE DWG. REV)		
QTY	PARTS LIST		

V=TURNED CONTACT (PCB SIDE CAN BE USED WITH POTTED COMPOUND)
*=VERSION: WITH HOOD, WITH CUT-IN, Ø8.2


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N K NIKHIL 25JUL2023 CHK M SZELAG 27JUL2023 APVD J DE BRUIN 27JUL2023		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 2768-mK ISO 8015		NAME M12 MALE, UNI CODE, 4P, 10.5MM SMT, DI V * - -	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-94887 APPLICATION SPEC 114-94781		SIZE CAGE CODE DRAWING NO RESTRICTED TO A2 00779 C=474329-E -	
MATERIAL - FINISH -		WEIGHT -		CUSTOMER DRAWING SCALE 5:1 SHEET 1 of 1 REV E2	



PCB-LAYOUT PROPOSAL



PART PACKED WITH HOOD



SCALE 2:1
3D VIEW

1. DRAWING SPECIFICATION ACCORDING TO DOCUMENT
5_3_16-DOC-1806-00915

2. COPLANARITY OF ALL CONTACTS AND CLIPS $\leq 0.1\text{MM}$