




Connectors > Pluggable IO Connectors & Cages



Form Factor: **QSFP28/56**

Pluggable I/O Product Type: **Cage Assembly**

Sealable: **Yes**

Circuit Application: **Signal**

Operating Temperature Range: **-40 – 85 °C [-40 – 185 °F]**

Features

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Post & Tail Length	2.05 mm[.081 in]

Contact Features

PCB Contact Termination Area Plating Material	Tin
---	-----

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
-----------------------------	------------------

Housing Features

Cage Material	Nickel Silver
---------------	---------------

Body Features

Heat Sink Style	Pin
Heat Sink Finish	Anodized Black



	.256 in
Heat Sink Height Class	SAN

Packaging Features

Packaging Method	Box & Tray
------------------	------------

Configuration Features

Number of Rear EONs per Port Column	1
Number of Ports	4
Port Matrix Configuration	1 x 4

Operation/Application

Pluggable I/O Applications	SFP+ Stacked Belly-to-Belly
Circuit Application	Signal

Product Type Features

Cage Type	Ganged
Thermal Accessory Type Included	Heat Sink
Form Factor	QSFP28/56
Pluggable I/O Product Type	Cage Assembly
Sealable	Yes

Electrical Characteristics

Data Rate (Max)	28 Gb/s
-----------------	---------

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Other

Included Lightpipe	Yes
EMI Containment Feature Type	Elastomeric Gasket
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2024 (241)
Candidate List Declared Against: JUNE 2024 (241)
Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C11-Z8
QSFP28 to QSFP28 Cable Assembly:
26 AWG

TE Part # 1551920-2
zQSFP+ connector assembly

TE Part # CAT-Q17-N490325
QSFP56 to QSFP56 Cable Assembly:
30 AWG

TE Part # CAT-Q17-N49011
QSFP56-Four SFP56 Cable Assembly:
30 AWG

TE Part # CAT-C11-Z806726
QSFP28 to QSFP28 Cable Assembly:
30 AWG

Also in the Series | **zQSFP+/QSFP28**

Heat Sinks(7)

Pluggable I/O Cable Assemblies(78)

Pluggable IO Connectors & Cages(424)

Customers Also Bought

TE Part #2132423-1
IMP100O,R,RA3P6C,RG,39

TE Part #2170872-1
Z-PACK TYPE/C MALE HDR 55P

TE Part #1-6450824-8
MBXL VERT HDR STR 2ACP

TE Part #1934937-1
Tinman 5pr 10col open hdr assy

TE Part #2-1734774-1
PCI EXP 3.1L 98 POS WHT 30u

TE Part #5-2170790-4
CAGE ASSY, 1X4, QSFP28, SPRING,
HS, LP

TE Part #6-1658043-2
MSB0.80RC-ASY080FL,GP,F,-TR

TE Part #6450834-1
MBXL R/A HDR STR 1P/8S/1P



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2170785-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2170785-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2170785-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

QSFP28/56 and zQSFP+ Interconnects

English

Product Specifications

Application Specification

English