




Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Number of Positions: 10

Terminal Block Connector Type: Plug

Connector System: Wire-to-Board

Centerline (Pitch): 5.08 mm [.2 in]

Number of Rows: 1

Features

Mechanical Attachment

Screw Plating Material	Nickel
Screw Material	Brass
Thread Size	M3

Body Features

Primary Product Color	Green
Product Orientation	Vertical

Packaging Features

Packaging Quantity	100
--------------------	-----

Contact Features

Contact Mating Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	15 A

Housing Features

--	--



Housing Material	PA 66
Centerline (Pitch)	5.08 mm[.2 in]

Product Type Features

Wire Protection	With
Terminal Block Connector Type	Plug
Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Wire Entry Location	Side
Stacking Configuration	Side Stackable
Stacked Levels	Without
Number of Positions	10
Number of Rows	1
Wire Entry Angle	90°

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Dimensions

Wire Size	30 – 12 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JUNE 2024 (241)

Candidate List Declared Against: JUNE 2024 (241)

SVHC > Threshold:
Pb (3% in Component Part)






Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-284061-0 TERMI-BLOK HDR 90, 5,08MMP. MU	 TE Part # 1-284065-0 TERMI-BLOK HDR 180, 5,08MM 0.M	 TE Part # 1-1546105-0 10 POS 5.08MM LH PLUG BLCK	 TE Part # 1-796637-0 10POS 5.08MM CE VRT HDR,TRM BK
 TE Part # 1-282815-0 TERMI-BLOK HEADER,ASSY90 10P.	 TE Part # 1-282825-0 TERMI-BLOK HEADER,ASSY90 10P.5	 TE Part # 1-2342083-0 10POS HDR 90 DEG,HT,5.08MM PITCH,TL2.6MM	 TE Part # 1-796639-0 10POS 5.08MM CE R/A HDR,TRM BK



TE Part # 1-796638-0
10POS 5.08MM CE R/A HDR,TRM BK

TE Part # 1-2342084-0
10POS HDR ST, HT, 5.08MM PITCH, TL 2.6MM

TE Part # 1-796636-0
10POS 5.08MM CE VRT HDR,TRM BK

Customers Also Bought

TE Part #1971845-2
2P, RAST 5 Tab Header, THV

TE Part #2232043-5
5P, RAST 5 Tab Header, THV

TE Part #1744429-6
3.96 EP HDR ASSY 6P W/PEGS, GW

TE Part #2029265-8
8P VAL-U-LOK VRTHDR W/PGS GW

TE Part #2232043-3
3P, RAST 5 Tab Header, THV

TE Part #2029181-5
5P VAL-U-LOK VRTHDR W/PGS GW

TE Part #1-2232511-4
4P, RAST 5 TAB HEADER, TH, VER, SEL

TE Part #1744429-2
3.96 EP HDR ASSY 2P W/PEGS, GW

TE Part #2-1971845-4
4P, RAST 5 Tab Header, THV

TE Part #1-1721260-1
OJ-SH-112LMH2

Documents

Product Drawings
TERMINAL BLOCK VERTICAL PLUG S
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_1-284041-0_C1.3d_igs.zip



English

Customer View Model

[ENG_CVM_1-284041-0_C1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1-284041-0_C1.2d_dxf.zip](#)

English

3D PDF

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-284041-0_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-284041-0_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-284041-0_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS](#)

English

[BUCHANAN PCB TERMINAL BLOCKS](#)

English

[1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG](#)

English

Product Specifications

[Application Specification](#)

English