

AMP


TE Internal #: 2-530666-6

Board-to-Board, 22 Position, 3.96 mm [.156 in] Centerline, Solder Eyelet, 22 Dual Positions, 2 Row, Green, Standard Edge Connectors

[View on TE.com >](#)



Connectors > PCB Connectors > Card Edge Connectors > Standard Edge Connectors



Connector System: **Board-to-Board**

Number of Positions: **22**

Centerline (Pitch): **3.96 mm [.156 in]**

Termination Method to Wire & Cable: **Solder Eyelet**

Number of Dual Positions: **22**

Features

Packaging Features

| | |
|--------------------|-----|
| Packaging Quantity | 90 |
| Packaging Method | Box |

Mechanical Attachment

| | |
|---------------------------------------|---------------|
| PCB Mount Retention | Without |
| Contact Retention Type Within Housing | Locking Lance |
| Mating Retention | Without |
| Mating Alignment | Without |
| PCB Mount Alignment | Without |
| Connector Mounting Type | Board Mount |

Contact Features

| | |
|---|------------------|
| Contact Underplating Material | Nickel |
| Contact Retention Within Housing | With |
| PCB Contact Termination Area Plating Material Finish | Bright |
| Contact Mating Area Plating Material Thickness | .76 µm |
| PCB Contact Termination Area Plating Material Thickness | 2.54 µm[100 µin] |
| Contact Mating Area Plating Material | Gold |
| Contact Base Material | Phosphor Bronze |
| PCB Contact Termination Area Plating Material | Tin |
| Contact Type | Socket |



| | |
|------------------------------|-----|
| Contact Current Rating (Max) | 5 A |
|------------------------------|-----|

Dimensions

| | |
|--------------------|------------------|
| Card Slot Depth | 7.49 mm[.29 in] |
| Connector Height | 11.68 mm[.46 in] |
| Row-to-Row Spacing | 5.08 mm[.2 in] |

Termination Features

| | |
|------------------------------------|-----------------------|
| Termination Method to PCB | Through Hole - Solder |
| Termination Post & Tail Length | 3.81 mm[.15 in] |
| Termination Method to Wire & Cable | Solder Eyelet |

Product Type Features

| | |
|-----------------------------------|-----------------------|
| Connector System | Board-to-Board |
| Connector & Housing Type | Receptacle |
| Connector & Contact Terminates To | Printed Circuit Board |

Configuration Features

| | |
|----------------------------------|--------------|
| Number of Positions | 22 |
| Number of Dual Positions | 22 |
| Number of Rows | 2 |
| Connector Contact Load Condition | Fully Loaded |
| PCB Mount Orientation | Vertical |

Body Features

| | |
|-----------------------|-------|
| Primary Product Color | Green |
|-----------------------|-------|

Housing Features

| | |
|--------------------|------------------------|
| Centerline (Pitch) | 3.96 mm[.156 in] |
| Housing Material | Glass-Filled Polyester |

Usage Conditions

| | |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 105 °C[-67 – 221 °F] |
|-----------------------------|----------------------------|

Operation/Application

| | |
|---------------------|-------|
| Circuit Application | Power |
|---------------------|-------|

Other

| | |
|--------------------|---------------------------|
| EU RoHS Compliance | Not Compliant |
| EU ELV Compliance | Compliant with Exemptions |



Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Not Compliant |
| EU ELV Directive 2000/53/EC | Compliant with Exemptions |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (13% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content | Not Low Halogen - contains Br or Cl > 900 ppm. |
| Solder Process Capability | Wave solder capable to 240°C |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



TE Part #1-5747299-4
15 RCPT SP/FMS SCRLK



TE Part #1-5745967-4
25 RCPT SP/FMS SCRLK



TE Part #1-5747872-6
15 PLUG SP/FMS INSRT



TE Part #5-747904-5
9 Plug Solder Cup, 30 gold, Ro



TE Part #641969-1
06P UMNL PIN HDR ASSY V2 NATL



TE Part #1744416-6
6 POS EP II HSG, GLOW WIRE



TE Part #641973-1
12P UMNL PIN HDR ASSY V2 NATL



TE Part #3-520404-2
ULTRA-FAST 187 ASY REC 16-14 AWG TPBR



TE Part #641967-1
04P UMNL PIN HDR ASSY POL NATL



TE Part #1-826629-6
16X1 AMPMODU II HDR ST

Documents

Product Drawings

CONN LOW PRO 22 POS 156X200C/L

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-530666-6_P.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-530666-6_P.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-530666-6_P.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Product Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

REPLACING CONTACTS IN AMP LOW PROFILE EDGE CONNECTORS

English

Agency Approvals

UL Report

English