

1544426-2  ACTIVE

TE Internal #: 1544426-2

Single-In-Line (SIL), 1.27 mm [.05 in] Centerline, Tin over Nickel,
Leadframes[View on TE.com >](#)

Connectors > PCB Connectors > Card Edge Connectors > Leadframes

Leadframe Type: **Single-In-Line (SIL)**Centerline (Pitch): **1.27 mm [.05 in]**PCB Thickness (Accepted): **.63 mm [.025 in]**Standoff Height: **1 mm [.039 in]**Leadframe Hold-Down Feature: **Without**

Features

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Configuration Features

Winding Direction	Down
-------------------	------

Packaging Features

Packaging Quantity	80000
--------------------	-------

Contact Features

Contact Base Material	Phosphor Bronze
-----------------------	-----------------

Leadframe Pin Length	9.7 mm[.382 in]
----------------------	-----------------

Leadframe Plating Material	Tin over Nickel
----------------------------	-----------------

Body Features

Leadframe Clip Length	1.5 mm[.059 in]
-----------------------	-----------------

Leadframe Thickness	.25 mm[.01 in]
---------------------	----------------

Leadframe Clip Type	Y1
---------------------	----

Leadframe Width	18.1 mm[.712 in]
-----------------	------------------

Leadframe Hold-Down Feature	Without
-----------------------------	---------

Dimensions

Leadframe Gap Size	.52 mm[.02 in]
--------------------	----------------

PCB Thickness (Accepted)	.63 mm [.025 in]
--------------------------	------------------

Standoff Height	1 mm [.039 in]
-----------------	----------------

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board
Leadframe Type	Single-In-Line (SIL)

Housing Features

Centerline (Pitch)	1.27 mm [.05 in]
--------------------	------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1544425-1
CTS 254 BRONZE PRE

Customers Also Bought



TE Part #281839-3
HOUSING HE13 HE14 COSI 2X3 P



TE Part #1676143-2
RN 0805 100R 0.1% 10PPM 1KRL



TE Part #1658621-8
34 NOVO MIL/CTR 15DP,LEAD FREE



TE Part #1617121-9
JMAC-26XM = M39016/9-062M



TE Part #4-1879133-4
RN 0603 2K49 0.1% 10PPM 1K RL



TE Part #1676238-2
RN 0805 1K62 0.1% 10PPM 1KRL



TE Part #1676451-2
RN 0805 86R6 0.1% 10PPM 1KRL



TE Part #CB03314003
RW-200-E-3/16-0-SP



TE Part #1617121-7
JMAC-26XL = M39016/9-062L



TE Part #1-2176379-7
RO 0805 158R 0.1% 10PPM 5K RL

Documents

Product Drawings

[CTS 1,27 BRONZE ET](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1544426-2_A_c-1544426-2-a.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1544426-2_A_c-1544426-2-a.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1544426-2_A_c-1544426-2-a.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.