


63493-1

✓ ACTIVE

TE Internal #: 63493-1
Pin, 2.84 mm [.112 in] Pin Diameter, 30 – 26 AWG, .05 – .15 mm²
Wire, 100 – 254 CMA, Open Barrel, Pre-Tin Plating, Length 25.15 mm [.99 in], Reel
[View on TE.com >](#)



Terminals & Splices > Crimp Wire Pins, Tabs & Ferrules



Crimp Wire Terminal Type: Pin
Mating Pin Diameter: 2.84 mm [.112 in]
Compatible Insulation Diameter Range: .63 – 1.15 mm, 1.15 mm [.025 – .045 in, .045 in]
Wire Size: .05 – .15 mm²

Features

Packaging Features

Packaging Quantity	5000
Packaging Method	Reel

Product Type Features

Compatible With Discrete Wire Type	Stranded
------------------------------------	----------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Contact Features

Crimp Wire Terminal Type	Pin
Mating Pin Diameter	2.84 mm [.112 in]
Barrel Type	Open
Terminal Plating Material	Pre-Tin
Contact Shape & Form	Round
Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------



Dimensions

Compatible Insulation Diameter Range	.63 – 1.15 mm, 1.15 mm[.025 – .045 in][.045 in]
Wire Size	100 – 254 CMA
Barrel Inside Diameter	.38 mm[.015 in]
Terminal Material Thickness	.3 mm[.012 in]
Overall Product Length	25.15 mm[.99 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 62074-1 PIN .125 (3.17 MM) 24-20 AWG 0.42 BR	 TE Part # 60115-4 PIN 125 RECEPTACLE 22-20 AWG BR	 TE Part # 62616-1 PIN .109 (2.77MM) 18-14 AWG 016BR	 TE Part # 1742377-2 PIN .080 DIA 30-26 AWG TPBR
 TE Part # 62820-1 PIN 093 CRIMP TAB 22-16 AWG PTPBR	 TE Part # 41854 PIN 093 (2.36 MM) REC 22-18 AWG TPBR	 TE Part # 626361-3 WALL PLUG PIN 0.5/1.5MM2 0.38X36.40 NIBR	 TE Part # 60115-1 PIN 125 REC 22-20 AWG BR
 TE Part # 62358-1 PIN .080 (2.03 MM) 24-20 AWG TPBR	 TE Part # 61674-1 PIN .109 .085 X .035 FLAT WIRE BR	 TE Part # 626361-1 WALL PLUG PIN 0.5/1.5 MM2 0.38X36.40 BR	 TE Part # 62505-1 PIN 130 22-18 AWG .0157 X 1.020 BR

Customers Also Bought

 TE Part #DT04-2P REC, 2P, GRY, N	 TE Part #DT06-2S PLG, 2P, GRY, N	 TE Part #CAT-D487-W416 Wedgelocks: DEUTSCH DT	 TE Part #CAT-D48-ST273 DEUTSCH Solid Contacts
 TE Part #CAT-AM71-CH8172 AMP SUPERSEAL 1.5MM, CONNECTOR HOUSING	 TE Part #281934-2 SINGLE WIRE SEAL		



Documents

Product Drawings

112 DIA PIN 30-26 012 PTPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_63493-1_D_c-63493-1-d.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_63493-1_D_c-63493-1-d.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_63493-1_D_c-63493-1-d.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.