

HC-EVO-B24-HLFD-PLBK - Housing



1420935

<https://www.phoenixcontact.com/us/products/1420935>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sleeve housing B24, for double locking latch, material: PA 6.6-FR, cable outlets: 1, straight/lateral, height: 63 mm, cable gland: none, Standard

Your advantages

- Flexible cable outlet direction, lateral or straight
- Lower costs than metal version
- Low weight
- Lower risk of condensation

Commercial data

Item number	1420935
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF57
Product key	BF7APL
Catalog page	Page 636 (C-2-2019)
GTIN	4055626249346
Weight per piece (including packing)	105 g
Weight per piece (excluding packing)	110 g
Customs tariff number	85389099
Country of origin	PL

HC-EVO-B24-HLFD-PLBK - Housing

1420935

<https://www.phoenixcontact.com/us/products/1420935>



Technical data


Notes

General	for contact inserts HC-B24, BB46, D64, DD108, M, K, HV10
---------	--

Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Product family	HC-EVO-B
Application	Standard
Type	B24
No. of cable outlets	1
Type	Low design
Shielded	no
Cable outlet	straight
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	43.8 mm
Height	63 mm
Length	120 mm

Material specifications

Flammability rating according to UL 94	V0 (Housing)
Housing material	PA 6.6-FR

Mechanical properties

Mechanical data

Locking type	Pin
--------------	-----

Mounting

Assembly note	The sleeve base housing must be supplemented with the EVO screw connection. The EVO screw connection is available in 4 sizes. It enables the creation of a straight or a lateral cable outlet. The EVO screw connection is assembled by hand or using a pipe wrench.
---------------	--

Environmental and real-life conditions

Ambient conditions

HC-EVO-B24-HLFD-PLBK - Housing



1420935

<https://www.phoenixcontact.com/us/products/1420935>

Degree of protection	IP66
Enclosure rating (NEMA)	12 (UL 50e)
Impact strength	IK09
Ambient temperature (operation)	-40 °C ... 125 °C

HC-EVO-B24-HLFD-PLBK - Housing


1420935

<https://www.phoenixcontact.com/us/products/1420935>



Drawings

Dimensional drawing



Dimensional drawing

HC-EVO-B24-HLFD-PLBK - Housing



1420935

<https://www.phoenixcontact.com/us/products/1420935>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1420935>

DNV

Approval ID: TAE000037S



cUL Recognized

Approval ID: E255026



UL Recognized

Approval ID: E255026



EAC

Approval ID: RU C-DE.AI30.B.01102

cULus Recognized

HC-EVO-B24-HLFD-PLBK - Housing



1420935

<https://www.phoenixcontact.com/us/products/1420935>

Classifications

ECLASS

ECLASS-11.0	27440202
ECLASS-12.0	27440202
ECLASS-13.0	27440202

ETIM

ETIM 9.0	EC000437
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.91 kg CO2e