



Passive Components > Resistors > Surface Mount Resistors > SMD Power Resistor: 7 Watt, 200-2M Ohm



Resistor Type: **Power Resistor**
Element Type: **Wire Wound**
Power Rating: **2 W**
Resistance Value: **180 Ω**
Resistance Class: **Up to 1kΩ**

[All SMD Power Resistor: 7 Watt, 200-2M Ohm \(316\)](#)

Features

Industry Standards

UL Flammability Rating	UL 94V-0
ESD HBM Classification	2
Moisture Sensitivity Level	1

Electrical Characteristics

Operating Voltage	300 V
Power Rating	2 W
Resistance Value	180 Ω
Resistance Class	Up to 1kΩ
Passive Component Tolerance	5 %

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1
---------------------	---

Termination Features

Surface Mount Resistor Termination Type	Solder
---	--------



Number of Terminations	2
------------------------	---

Dimensions

Product Height	3.55 mm[.14 in]
Product Length	6.7 mm[.264 in]
Product Width	4 mm[.157 in]

Usage Conditions

Temperature Coefficient	±200 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 1879233-9
SMW5 R22 5%

TE Part # CAT-C339-SM1
SMD Power Resistor: 7 Watt, 200-2M Ohm

TE Part # 7-2176616-9
SMQW2W 180R 5%

Also in the Series | CGS SM

Battery Holders(1)

Expanded Beam Fiber Optics(6)

LC Connectors(1)

RJ14 Connectors(1)

RJ22 Connectors(1)

RJ25 Connectors(1)

SC Connectors(2)

Customers Also Bought

TE Part #1-1879233-3
SMW5 R33 5%

TE Part #2176232-2
3522 150K 1% 3W

TE Part #6-1676966-9
SMW2 68R 5%

TE Part #T4062124004-001
RPC-M8-4MS-0.5SH-M8-4FR-PUR



TE Part #87227-7
14 MODII HDR DRST UNSHRD .100

TE Part #282834-4
TERMI-BLOK PCB MOUNT, 90 4P.

TE Part #5-2213767-1
AV19 DPM 3A MOVE RING LED
YELLOW 24V

TE Part #2-2176217-2
CPF A 0805 180R 0.1% 25PPM 1K RL

TE Part #9998552005
DWTC-16/4-X-STK

TE Part #K1142884
Battery Disconnecter 35-210-051-R-900

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-1676966-9_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_7-1676966-9_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_7-1676966-9_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English

SMD Moulded Power Resistor - Type SM Series - Tyco Electronics Passives

English