



| REVISIONS |     |                          |           |     |      |
|-----------|-----|--------------------------|-----------|-----|------|
| P         | LTR | DESCRIPTION              | DATE      | DWN | APVD |
|           | A2  | 2-1776315-3 OBSOLESCENCE | 22MAY2024 | SN  | PS   |

1. MATERIAL:  
HOUSING: POLYAMIDE 6 UL94V-2.  
COLOR: NATURAL (OFF WHITE).  
TUBULAR CONTACT: BRASS, TIN PLATED.  
SCREW: SEE TABLE  
WIRE PROTECTOR: STAINLESS STEEL
2. ELECTRICAL:  
CURRENT RATING: 65A, 600V.  
WIRE RANGE: 6-14 UL AND 6-22 AWG FOR (CSA)
3. CONTINUOUS WORKING TEMP.: 100°C MAX.
4. CUTTING PROJECTION CAN BE ON BOTH SIDES  
DEPENDING ON CUTTING LOCATION.
5. CUTTING BURR MAX. 1mm ALLOWED.



|                |                             |       |       |                   |                |
|----------------|-----------------------------|-------|-------|-------------------|----------------|
| OBSOLETE       | NICKEL PLATED BRASS         | 14.5  | 40.2  | TSB200003KDS      | 2-1776315-3    |
| OBSOLETE       | NICKEL PLATED BRASS         | —     | 25.7  | TSB200002KDS      | 2-1776315-2    |
|                | TRIVALENT ZINC PLATED STEEL | 145.0 | 170.7 | TSB200012KDS      | 1-1776315-2    |
|                | TRIVALENT ZINC PLATED STEEL | 130.5 | 156.2 | TSB200011KDS      | 1-1776315-1    |
|                | TRIVALENT ZINC PLATED STEEL | 116.0 | 141.7 | TSB200010KDS      | 1-1776315-0    |
|                | TRIVALENT ZINC PLATED STEEL | 101.5 | 127.2 | TSB200009KDS      | 1776315-9      |
|                | TRIVALENT ZINC PLATED STEEL | 87.0  | 112.7 | TSB200008KDS      | 1776315-8      |
|                | TRIVALENT ZINC PLATED STEEL | 72.5  | 98.2  | TSB200007KDS      | 1776315-7      |
|                | TRIVALENT ZINC PLATED STEEL | 58.0  | 83.7  | TSB200006KDS      | 1776315-6      |
|                | TRIVALENT ZINC PLATED STEEL | 43.5  | 69.2  | TSB200005KDS      | 1776315-5      |
|                | TRIVALENT ZINC PLATED STEEL | 29.0  | 54.7  | TSB200004KDS      | 1776315-4      |
|                | TRIVALENT ZINC PLATED STEEL | 14.5  | 40.2  | TSB200003KDS      | 1776315-3      |
|                | TRIVALENT ZINC PLATED STEEL | —     | 25.7  | TSB200002KDS      | 1776315-2      |
|                | TRIVALENT ZINC PLATED STEEL | —     | 11.2  | TSB200001KDS      | 1776315-1      |
| SCREW MATERIAL |                             | DIM B | DIM A | T & B PART NUMBER | TE PART NUMBER |

1776315-4 AS SHOWN

|                                        |  |                       |         |                                                                 |                    |
|----------------------------------------|--|-----------------------|---------|-----------------------------------------------------------------|--------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN<br>S SCHLEGEL     | 3/21/05 | TE Connectivity Ltd.                                            |                    |
|                                        |  | CHK<br>C RICHARD      | 3/21/05 |                                                                 |                    |
|                                        |  | APVD<br>C RICHARD     | 3/21/05 | NAME<br>14.5MM PITCH WIRE PROTECTOR<br>65A HIGH VOLTAGE VERSION |                    |
|                                        |  | PRODUCT SPEC<br>—     |         | —                                                               |                    |
|                                        |  | APPLICATION SPEC<br>— |         | SIZE<br>A3                                                      | RESTRICTED TO<br>— |
|                                        |  | WEIGHT<br>—           |         | CAGE CODE<br>00779                                              | REV<br>A2          |
|                                        |  | CUSTOMER DRAWING      |         | SCALE<br>NTS                                                    | SHEET<br>1 OF 1    |