




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**

Wire Size: **.32 – .82 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Industry Standards

Compatible With Agency/Standards Products	UL
UL Flammability Rating	UL 94V-2

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Electrical Characteristics

Voltage Rating	600 V
----------------	-------

Body Features

Insulation Material	Nylon
---------------------	-------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple



Other

Barrel Color	Red
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Packaging Features

Packaging Quantity	1400
Packaging Method	Strip/Reel

Dimensions

Product Length	21.75 mm[.855 in]
Compatible Insulation Diameter Range	3.43 mm[.135 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	.32 – .82 mm²

Product Type Features

Insertion Force	Normal
-----------------	--------

Contact Features

Quick Disconnect Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Unplated
Crimp Type	F-Crimp
Barrel Type	Closed

Usage Conditions

Insulation Option	Fully Insulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 7-2151034-7
[OCEAN_2.0_SPARE_PART_KIT-176O](#)



TE Part # 90390-3
[DIES ULTRA-FAST FASTON 22-18 DIE SET](#)



TE Part # 58628-2
[PROCRMP DIESET 26-14 ULTRAFAST](#)



TE Part # 58628-1
[PROCRIMP T&D 26-14 ULTRAFAST](#)



TE Part # 2151034-2
[OCEAN_2.0_APPLICATOR-S-176O-SSA](#)

Also in the Series | [Ultra-Fast 250](#)



Automotive Housings(3)



Quick Disconnects(49)

Customers Also Bought



TE Part #DT04-2P-E004
REC, 2P, BLK, N



TE Part #1658610-3
15 POS HDF RCPT, MS, LEAD FREE



TE Part #5-2176070-8
3521 2K4 1% 2W



TE Part #1658622-3
16 NOVO MIL/CTR 30DP,LEAD FREE




TE Part #2176349-7
CRGCQ 2512 33R 1%



TE Part #2-2176327-5
CRGP 0805 1K0 1%



TE Part #1-2176327-7
CRGP 0805 220R 1%



TE Part #1-776087-1
23POS,PIN DIA 1.3,HDR ASSY,90DEG, COD 1



TE Part #770855-1
03P FAN MOTOR CONN HSG



TE Part #41616
250 FASTON TAB BR

Documents

Product Drawings

ULTRA-FAST 250 ASSEMBLY TAB 22-18 AWG BR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-520102-1_N.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2-520102-1_N.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-520102-1_N.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL](#)

English