

2307526-1

 DO NOT USE FOR NEW DESIGN

## NECTOR | NECTOR M Series

TE Internal #: 2307526-1

TE Internal Description: NECTOR M 7P SEALED SOCKET PCB

CODE A

[View on TE.com >](#)

## Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU

Compliant with Exemptions

EU ELV Directive 2000/53/EC

Compliant with Exemptions

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2024  
(241)Candidate List Declared Against: JUNE  
2024 (241)

SVHC &gt; Threshold:

Pb (1.6% in Component Part)

## Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Low Halogen - contains Br or Cl > 900  
ppm.

Solder Process Capability

Not reviewed for solder process capability

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 2307526-2  
NECTOR M 7P SEALED SOCKET PCB  
CODE B


## Also in the Series | NECTOR M Series



Connector Hardware(4)



PCB Headers & Receptacles(2)



Standard Circular Connectors(45)

## Customers Also Bought




TE Part #767514-2  
INSERTER, 76 POS. R/A PLUG



TE Part #820941-000  
202K121-3-01/42-0



TE Part #7-1617791-0  
3SBM6004R2=4PDT 1/5 SIZE  
LATCHING RELAY



TE Part #1484613-2  
RECP ASSY, SZ 2, ARINC 600



TE Part #2213588-1  
NECTOR M SKT CAP 5P SEALED



TE Part #767158-5  
190 POS. R/A PLUG ASSY



TE Part #5-146130-8  
18 MODII HDR DRST SFMNT B/A LF



TE Part #1879999-1  
NECTOR M 5P T-S SEAL  
CONNECTOR CODE A



## Documents

### Product Drawings

#### NECTOR M 7P SEALED SOCKET PCB CODE A

English

---

### CAD Files

#### Customer View Model

[ENG\\_CVM\\_CVM\\_2307526-1\\_A.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_2307526-1\\_A.3d\\_stp.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_2307526-1\\_A.2d\\_dxf.zip](#)

English

### 3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Agency Approvals

#### NECTOR M CONNECTORS CB TEST CERTIFICATE TO IEC 61535

English

#### NECTOR M CONNECTORS CB TEST REPORT TO IEC 61535

English