




PIDG

TE Internal #: 323011
Slotted Ring Tongue Terminal, 26 – 22 AWG, #6 / M3.5 Stud, 3.68 mm [.145 in] Stud Diameter, Closed Barrel, Straight, Tin Plating, PIDG

[View on TE.com >](#)

Terminals & Splices > Ring Terminals > PIDG Slotted Ring Tongue Terminals



Ring Terminal Product Type: **Slotted Ring Tongue Terminal**

Wire Size: **202 – 810 CMA**

Stud Size: **#6, M3.5**

[All PIDG Slotted Ring Tongue Terminals \(6\)](#)

Features

Body Features

Product Weight	.294 g
----------------	--------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Electrical Characteristics

Voltage Rating	300 V
----------------	-------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Product Type Features

Terminal Features	Slotted
Ring Terminal Product Type	Slotted Ring Tongue Terminal



Stud Size	#6, M3.5
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Dimensions

Wire Size	202 – 810 CMA
Stud Diameter	3.68 mm[.145 in]
Tongue Thickness	.79 mm[.031 in]
Product Length	18.26 mm[.719 in]
Compatible Insulation Diameter (Max)	2.03 mm[.08 in]
Compatible Insulation Diameter Range	1.27 – 2.03 mm[.05 – .08 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 169485
DAHT PIDG PG 26-22 ASSY



TE Part # 59275
T-HEAD PIDG PG SH 26-20 ASSY



TE Part # 69344
PIDG 26-22 DIE SET




TE Part # 46121
DAHT PG PIDG 26-22 ASSY

Also in the Series | PIDG



Compression Connectors(17)



Crimp Wire Pins, Tabs & Ferrules(41)



Hand Crimping Tools(2)




Knife Disconnects(11)



Quick Disconnects(38)



Ring Terminals(588)



Spade Terminals(228)



Special Purpose Terminals(1)



[Splices\(41\)](#)

Customers Also Bought




TE Part #1-1318118-9
[DYNAMIC D-2100 REC HSG 20P](#)



TE Part #CAT-H3399-CH8172
[Heavy Duty Sealed Connector Series Housings](#)



TE Part #1-175196-2
[DYNAMIC D-3 REC CONT/L AU 0.38](#)



TE Part #1776263-2
[2P TB Plug,w/interlock,90deg,5mm, Blue](#)



TE Part #7-1393254-9
[W92-X112-40=M6/M7/M9/W6/W7](#)




TE Part #1393255-8
[W93-X112-30=M6/M7/M9/W6/W7](#)



TE Part #1-2201855-2
[MINI I/O PLUG KIT TYPE II M](#)



TE Part #1703838-1
[SLIDE,TAB HSG GROUP A](#)



TE Part #61498-1
[SPADE 28-22 AWG .0157 X .310 BR](#)

Documents

Product Drawings

[TERMINAL,PIDG R SLTD 26-22 6](#)

English

CAD Files

[3D PDF](#)

English

Customer View Model

[ENG_CVM_323011_R.3d_igs.zip](#)



English

Customer View Model

[ENG_CVM_323011_R.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_323011_R.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

[UL Report](#)

English