

10EJM1

 SUPERSEDED

Corcom | Corcom EJM

TE Internal #: 6609985-4


TE Internal Description: 10EJM1=F8186

IEC Filtered Inlets, Corcom EJM Series

[View on TE.com >](#)



EMI & EMC Solutions > EMI Filters > Power Entry Modules > IEC Filtered Inlets, Corcom EJM Series



Filter Type: **Power Line**

Product Orientation: **Right Angle**

Leakage Current (Max) (120VAC, 60Hz): **10 μ A**

Leakage Current (Max) (250VAC, 50Hz): **17 μ A**

Current Rating: **10 A**

[All IEC Filtered Inlets, Corcom EJM Series \(0\)](#)

Features

Mechanical Attachment

Panel Mount Feature Type	Mounting Holes, Mounting Ears (Horizontal)
--------------------------	--

Product Type Features

Ground Choke Option	No
Filter Type	Power Line
Output Termination Type	.250" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 320/C-14

Body Features

Product Orientation	Right Angle
---------------------	-------------

Electrical Characteristics

Leakage Current (Max) (120VAC, 60Hz)	10 μ A
Leakage Current (Max) (250VAC, 50Hz)	17 μ A
Current Rating	10 A



Operating Voltage250 VAC

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series |

Customers Also Bought





TE Part #8-2176305-7
RP 1E 0.1W 845R 0.1% 25PPM 5K RL



TE Part #625296-000
D-141-0114



TE Part #625294-000
D-141-0112



TE Part #786862-5
50 50SR PANEL MOUNT RCPT S/A




TE Part #745215-7
PLUG ASSY,37P,HDE,AP




TE Part #EP3166-000
0026G8424-9



TE Part #228658-1
JACK,REAR MOUNT,SERIES N



TE Part #5-192041-0
LAIV 0.12mm(.005) GOLD



TE Part #1055824-1
HD TRIM POINTING TL .085 CABLE

Documents

CAD Files

Customer View Model

ENG_CVM_CVM_6609985-4_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_6609985-4_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6609985-4_A.3d_stp.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_6609985-4_1.3d_igs.zip

English

Customer View Model

ENG_CVM_6609985-4_1.3d_stp.zip

English



Customer View Model

[ENG_CVM_6609985-4_1.2d_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654001_CORCOM_PRODUCT_GUIDE_EEJ_SERIES](#)

English

[Corcom Combined Selector Charts](#)

English

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English