




Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Cluster Blocks



Number of Circuits: 3

Primary Product Material: PBT

Wire Size: .326 – 5.26 mm²

Operating Temperature Range: -20 – 120 °C [-4 – 248 °F]

Features

Product Type Features

Compatible With Discrete Wire Type	Lead Wire
------------------------------------	-----------

Contact Features

Mating Pin Diameter	3.18 mm[.125 in]
---------------------	------------------

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Mechanical Attachment

Mount Diameter	20.7 mm[.815 in]
Block Mounting Configuration	1 Forward - 2 Back

Dimensions

Product Length	50.17 mm[1.97 in]
Wire Size	.326 – 5.26 mm ²

Body Features

Primary Product Color	Natural
Primary Product Material	PBT



Configuration Features

Number of Circuits	3
--------------------	---

Usage Conditions

Operating Temperature Range	-20 – 120 °C[-4 – 248 °F]
-----------------------------	---------------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # 1217670-1 CLSTR BLK RCPT AMVAR 400-1600	 TE Part # 62244-3 125 PIN RCPT 18-16	 TE Part # 1742657-1 CLUSTER BLOCK RECP 22-18 020TP	 TE Part # 1217176-1 CLUSTER BLOCK RECPT.
 TE Part # 62243-3 125 PIN RECEPTACLE 14-10	 TE Part # 63453-1 Cluster Block Recpt Amplivar 400-1600	 TE Part # 63455-1 Cluster Block Recpt Amplivar 4000-8500	 TE Part # 1217174-1 Cluster Block Recpt Amplivar 1500-4200
 TE Part # 1217672-1 CLSTR BLK RCPT AMVAR 4000-8500	 TE Part # 2825316-1 CLUSTER BLOCK HOUSING GWT	 TE Part # 62243-5 125 PIN RECEPTACLE 14-10	 TE Part # 1217176-5 CLUSTER BLK RECP,18-16 020PHBR
 TE Part # 62244-6 125 PIN RECEPTACLE 18-16	 TE Part # 1217175-1 CLUSTER BLOCK RECPT.	 TE Part # 63454-1 Cluster Block Recpt Amplivar 1500-4200	 TE Part # 1217172-1 Cluster Block Recpt Amplivar 400-1600
 TE Part # 1217671-1 CLSTR BLK RCPT AMVAR 1500-4200	 TE Part # 1217173-1 Cluster Block Recpt Amplivar 4000-8500	 TE Part # 316293-3 3.2 CLUSTER BLOCK HSG, LCP TYPE	

Customers Also Bought





TE Part #DT04-2P
REC, 2P, GRY, N



TE Part #DT06-2S
PLG, 2P, GRY, N



TE Part #CAT-D487-W416
Wedgelocks: DEUTSCH DT




TE Part #CAT-D48-ST273
DEUTSCH Solid Contacts



TE Part #CAT-AM71-CH8172
AMP SUPERSEAL 1.5MM,
CONNECTOR HOUSING



TE Part #206070-8
CABLE CLAMP KIT #17



TE Part #281934-2
SINGLE WIRE SEAL

Documents

Product Drawings

HSG .125 CLUSTER BLOCK NAT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1217261-1_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1217261-1_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1217261-1_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Magnet Wire Terminals & Splices

English

Product Specifications

Engineering Report

English