




Terminals & Splices > Splices



Splice Type: **Pigtail Splice**
Wire Size: **.8 – 2.5 mm²**
Sealable: **No**
Splice Capacity: **3**

Features

Electrical Characteristics

Operating Voltage	250 V
-------------------	-------

Termination Features

Termination Method to Wire & Cable	Crimp
Crimp Width	2.79 mm[.11 in]

Packaging Features

Packaging Quantity	20000
Packaging Method	Strip

Contact Features

Terminal Plating Material	Unplated
Contact Base Material	Phosphor Bronze
Barrel Type	Open

Body Features

Product Weight	.214 g
Splice Features	Serrated



Configuration Features

Strip Orientation	End Feed
Splice Capacity	3
Number of Serrations	7

Product Type Features

Splice Type	Pigtail Splice
Sealable	No
Compatible With Discrete Wire Type	Solid, Magnet Wire

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	1500 – 5000 CMA
Terminal Material Thickness	.51 mm[.02 in]
Product Length	5.72 mm[.225 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-65 – 150 °C[-85 – 302 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241)



Candidate List Declared Against: JUNE 2024 (241)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 737060-1
AMPLIVAR SPL 5 SERR W/INS SUP



TE Part # 280538-1
AMPLIVAR Splice, unplated version




TE Part # 140837-2
SPLICE AMPLIVAR




TE Part # 2150115-2
OCEAN_2.0_APPLICATOR-E-110F-SEA

Also in the Series | AMPLIVAR



Crimp Wire Pins, Tabs & Ferrules(4)



Magnet Wire Terminals(4)



PCB Terminals(1)



Quick Disconnects(40)



Ring Terminals(28)



Splices(71)


Customers Also Bought




TE Part #1971777-3
PTL TPA HIGH TEMP 1 x 3 BLACK




TE Part #5-2232263-3
PTL 1X3 CAP PANEL MT GLW WIRE
KEY A DGR



TE Part #360051-1
CLUSTER BLOCK




TE Part #62305-2
AMVAR SPLC 600-3000 016TPBR



TE Part #62304-2
AMVAR SPLC 600-3000 020TPBR




TE Part #2232901-1
AMP POWER DBL LOCK REC (L)



TE Part #62000-2
SPLICE AMVAR 600-3000 020TPBR



TE Part #62131-8
CLSTR PIN RCPT



TE Part #659307-1
SHEAR BLADE, LOWER



TE Part #240635-1
FINGER, FEED

Documents

Product Drawings
AMPLIVAR-VERBINDER

English

CAD Files
3D PDF

English

Customer View Model
ENG_CVM_964156-1_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_964156-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_964156-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654742_HOUSEHOLD_APPLIANCES_RAST5](#)

English

Magnet Wire Terminals & Splices

English

Product Specifications

[Application Specification](#)

English

[AMPLIVAR 7 Serration Pigtail Splice](#)

English