

SACC-SQ-M12MS-4CON-20-L180 - Device connector front mounting



1456417

<https://www.phoenixcontact.com/us/products/1456417>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, Universal, 4-position, Pin, straight, M12, coding: A, Front mounting, Square flange, Wave soldering, 0.34 mm²

Your advantages

- Easy PCB assembly: one-piece connectors for wave soldering
- Standard pin assignments for signal and power transmission with a uniform design-in design
- SPEEDCON fast locking system reduces cabling times

Commercial data

Item number	1456417
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AB26
Product key	ABQEGK
Catalog page	Page 240 (C-2-2013)
GTIN	4046356617024
Weight per piece (including packing)	11.57 g
Weight per piece (excluding packing)	10.64 g
Customs tariff number	85366990
Country of origin	DE

SACC-SQ-M12MS-4CON-20-L180 - Device connector front mounting



1456417

<https://www.phoenixcontact.com/us/products/1456417>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Mounting

Mounting type	Front mounting Square flange 20 mm side length
Assembly note	20 mm side length

Product properties

Product type	Circular connectors (device side)
Sensor type	Universal
Number of positions	4
No. of cable outlets	1
Shielded	no
Coding	A
Thread type	M12

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	V0
Seal material	FKM
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Rated surge voltage	2.5 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	250 V
Nominal current I_N	4 A
Max. conductor resistance	57.6 $\text{m}\Omega/\text{m}$

Connection data

SACC-SQ-M12MS-4CON-20-L180 - Device connector front mounting



1456417

<https://www.phoenixcontact.com/us/products/1456417>

Conductor connection

Connection method	Wave soldering
Contact connection type	Pin
Conductor cross section	0.34 mm ²
Tightening torque	Installation-side

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Connector

Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M12
Coding	A

Cable/line

Signal type/category	Universal
Wire diameter incl. insulation	1.2 mm ±0.07 mm
Cable cross section	0.34 mm ²
Conductor structure signal line	7x 0.25 mm
Thickness, insulation	0.21 mm
Nominal voltage, cable	300 V
Test voltage, cable	2000 V AC
Cable resistance	≤ 57.6 mΩ/m
Cable insulation resistance	≥ 20 MΩ*km
Ambient temperature (operation)	-40 °C ... 85 °C (cable, fixed installation) -25 °C ... 85 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket) -40 °C ... 85 °C (without mechanical actuation) -25 °C ... 85 °C (Cable, flexible installation) -40 °C ... 85 °C (cable, fixed installation)

Standards and regulations

M12

SACC-SQ-M12MS-4CON-20-L180 - Device connector front mounting



1456417

<https://www.phoenixcontact.com/us/products/1456417>

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101

SACC-SQ-M12MS-4CON-20-L180 - Device connector front mounting




1456417

<https://www.phoenixcontact.com/us/products/1456417>

Drawings

Schematic diagram



Pin assignment M12 plug, 4-pos., A-coded, view plug side

SACC-SQ-M12MS-4CON-20-L180 - Device connector front mounting



1456417

<https://www.phoenixcontact.com/us/products/1456417>

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1456417>

cUL Recognized Approval ID: E118976-20100522				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	250 V	4 A	22 - 22	-

UL Recognized Approval ID: E118976-20100522				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	250 V	4 A	22 - 22	-

cULus Recognized Approval ID: E221474-20140616				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	250 V	4 A	-	-

cULus Recognized

SACC-SQ-M12MS-4CON-20-L180 - Device connector front mounting



1456417

<https://www.phoenixcontact.com/us/products/1456417>

Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-SQ-M12MS-4CON-20-L180 - Device connector front mounting



1456417

<https://www.phoenixcontact.com/us/products/1456417>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	48c21c53-4f78-43e9-a303-5e131950bdab

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com