

4DB-R108-05

✓ ACTIVE

Buchanan | [Buchanan 4DB Series](#)

TE Internal #: 7-1437667-4

5 Position Barrier Strip, Dual Barrier, Printed Circuit Pin Bottom

Termination, Wire-to-Board, 8.26 mm [.325 in] Centerline, Buchanan

4DB Series

[View on TE.com >](#)



Connectors > Terminal Blocks & Strips > Barrier Strips



Number of Positions: 5

Barrier Strip Style: **Dual Barrier**

Bottom Termination Type: **Printed Circuit Pin**

Connector System: **Wire-to-Board**

Centerline (Pitch): **8.26 mm [.325 in]**

Features

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Package
Packaging Quantity	40

Operation/Application

Circuit Application	Power
---------------------	-------

Mechanical Attachment

Top Termination Type	Wire Clamp Combo Head
Mounting Options	None
Screw Plating Material	Zinc Chromate
Screw Material	Steel
Thread Size	6-32
Screw Head Type	Wire Clamp Combo Head
Connector Mounting Type	Board Mount



Contact Features

Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Current Rating (Max)	20 A, 10 A

Dimensions

Product Length	42.93 mm[1.69 in]
Wire Size	22 – 12 AWG

Housing Features

Housing Material	Thermoplastic Polyamide
Centerline (Pitch)	8.26 mm[.325 in]

Product Type Features

Block Style	Flat Bottom
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Body Features

Primary Product Color	Black
Product Orientation	Right Angle
Barrier Strip Style	Dual Barrier

Configuration Features

Number of Levels	1
Number of Positions	5
Number of Rows	1

Termination Features

Bottom Termination Type	Printed Circuit Pin
-------------------------	---------------------

Electrical Characteristics

Operating Voltage	300 V, 150 V
-------------------	--------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | Buchanan 4DB Series




Customers Also Bought







TE Part #2-1437565-7
FSM2JSMA=SMT,TACTILE,PB SWITCH




TE Part #725964-2
250 FASTON TAB TPBR



TE Part #3-520124-2
187 ULTRA-FAST ASY REC 16-14 AWG TPBR



TE Part #3-520406-2
ULTRA-FAST 250 ASY REC 16-14 AWG TPBR



TE Part #5104338-4
A/L LOW PRO HDR 20P VERT HT



TE Part #1623244-1
CRG0805 1% 51K



TE Part #1-2176337-7
CRGCQ 0402 220R 1%



TE Part #7-1437667-2
4DB-R108-03=4DB ASSEMBLY



TE Part #2-35108-1
TERMINAL,PIDG R 12-10 8



TE Part #5-1393788-5
V23079D1001B301

Documents

Product Drawings

4DB-R108-05=4DB ASSEMBLY

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_7-1437667-4_B1.3d_igs.zip

English

Customer View Model

ENG_CVM_7-1437667-4_B1.3d_stp.zip

English

Customer View Model

ENG_CVM_7-1437667-4_B1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_7-1437667-4_E.3d_igs.zip

English



Customer View Model

[ENG_CVM_CVM_7-1437667-4_E.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-1437667-4_E.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[BUCHANAN TERMINAL BLOCKS CATALOG - BARRIER STRIPS](#)

English

[1-1773458-2_BARRIER_STRIPS_QUICK_REFERENCE_GUIDE](#)

English