




RJ45 AND USB 2.0 Contacts, Tools, and Accessories



660-024 and -023 Protective Covers, Attached to Panel for 38999 Type Receptacle Connectors


How To Order							
Sample Part Number	660	-024	M	17	H	5	-01
Series	660 = Series 66						
Cover Type	-024 = metal receptacle cover -023 = metal plug cover						
Material and Finish	See Material and Finish Table						
Shell Size	15, 17, 19						
Lanyard Type	D, S, F, G, H, K, R, T, U (See Lanyard Type Table)						
Lanyard Length	Length in inches						
Ring Style Dash No.	(See Table I and II) omit for "SK" slip knot attachment						

Table I: Dash No. for Small Ring			
Dash No.	P	Dash No.	P
01	.140 (3.6)	06	.125 (3.2)
02	.182 (4.6)	07	.218 (5.5)
03	.191 (4.9)	09	.156 (4.0)
04	.197 (5.0)	00	no eyelet
05	.167 (4.2)	WS	with strap



For attachment to panel

Table II: Dash No. for Solid Ring		
Dash No.	Shell Size	N
19	15	1.141 (29.0)
21	17	1.266 (32.2)
23	19	1.391 (35.3)







SOLID RING (with tab)

For attachment behind jam nut


Dimensions			
Shell Size	A Thread	F	ØG Max
15	1.0000	1.300 (33.0)	1.260 (32.0)
17	1.1875	1.457 (37.0)	1.457 (37.0)
19	1.2500	1.575 (40.0)	1.535 (39.0)

Lanyard Type	
Sym	Attachment
D	Bead chain, cres, passivated, with terminal
E	Link chain, cres, passivated, with clevis terminal
F	Wire rope, nylon jacket w/terminal
G	Nylon rope
H	Wire rope, fluoropolymer jacket with terminal
K	Nylon rope (olive drab color)
N	Attachment omitted
R	Wire rope, pvc jacket w/terminal
T	Wire rope, no jacket, w/terminal
S	#8 Sash chain, cres, passivate
U	Wire rope, polyurethane jacket with terminal
SK	Nylon rope (black) with slip knot

Lanyard Types		
		
Bead Chain (Type D)	Sash Chain (Type S)	Rope (Types F, G, H, K, R, T, U)



660-024 Receptacle Cover



NOTES

- Length tolerance for Sash Chain (S) is ± 1 link, for all other attachments ± .25.
- For plug covers contact factory
- Material and Finish
 - Gasket: Silicone
 - Hardware, Rivet: Stainless Steel/ Passivate

Materials and Finishes ¹	
NF	Aluminum/Cadmium, olive drab
ME	Aluminum/Electroless nickel
MT	Aluminum/ Nickel PTFE
ZR	Aluminum/ Black zinc-nickel
ZI	Stainless Steel/ Passivate

MIL-DTL-38999 Type

M