



Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Locks & Position Assurance



Connector & Contact Retention Accessory Type: **Retainer**
Primary Product Color: **Black**
Primary Product Material: **PBT GF**
Operating Temperature Range: **-40 – 120 °C [-40 – 248 °F]**
EU RoHS Compliance: **Compliant**

Features

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Method	Bag
Packaging Quantity	15000

Other

Serviceable	Yes
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Type Features

Connector & Contact Retention Accessory Type	Retainer
--	----------

Body Features

Primary Product Color	Black
Primary Product Material	PBT GF

Usage Conditions

Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]
-----------------------------	----------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-M8793-CH8172
MQS, CONNECTOR HOUSING

Customers Also Bought

TE Part #5-160558-1
FF 250 REC 0.5-1.5MM2 BR

TE Part #962875-3
MT2 REC 1.6 Contact SWS Au

TE Part #2-2141047-5
6POS MIXED MQS REC COD B

TE Part #1813112-1
MCP 1.5&2.8 HYB 28P PLUG ASS'Y



TE Part #1-2209544-9
60POS,AMP 0.64,REC HSG ASSY,SLD,
COD Z

TE Part #1-2209545-9
94POS,MQS,REC HSG ASSY,SLD,COD
Z

TE Part #2-2355514-1
4POS,MCON 1.2,REC HSG ASSY,SLD

TE Part #2434841-3
MCON 1.2,TERMINAL,CB,REC SRC AG

TE Part #7-2435189-3
MCON 1.2,TERMINAL,LL REC SWS AG

TE Part #2434761-1
AMP MCP 2.8K,TERMINAL,SWS

Documents

Product Drawings

MQS LOCKING DEVICE FOR4P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1534131-1_A1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1534131-1_A1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1534131-1_A1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English