



Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Number of Positions: 4

Terminal Block Connector Type: **Header**

Connector System: **Wire-to-Board**

Centerline (Pitch): **10.16 mm [.4 in]**

Number of Rows: 1

Features

Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	3.5 mm[.138 in]

Body Features

Primary Product Color	Green
Product Orientation	Vertical

Packaging Features

Packaging Quantity	100
--------------------	-----

Contact Features

Contact Mating Area Plating Material	Tin
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	15 A

Housing Features

Housing Material	PA 66
Centerline (Pitch)	10.16 mm[.4 in]



Product Type Features

Header Type	Fully Shrouded
Terminal Block Connector Type	Header
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Stacking Configuration	Side Stackable
Number of Positions	4
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Dimensions

Wire Size	30 – 12 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC




Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 284051-4
TERMI-BLOK VERTICAL PLUG STACK



TE Part # 284045-4
TERMI-BLOK VERTICAL PLUG STACK



TE Part # 1776161-4
4P TERMI-BLOK HDR,HIGH TEMP




TE Part # 282809-4
TERMI-BLOK PLUG STACKING 4P.10

Customers Also Bought



TE Part #5788793-2
09 HTMSFL PLUG RA 318 (SL,BL)



TE Part #103310-1
010 LOPRO HDR RA 15DP



TE Part #556137-1
HSG,AMPINNERGY WTW,1 POS, WHITE



TE Part #1393127-9
PRD-11AG0-120=PRD




TE Part #2057427-3
IMP100S,H,V2P10C,UG,LEW46,5.5




TE Part #2057745-3
IMP100S,H,V2P16C,UG,LEW46,5.5



TE Part #2057747-3
IMP100S,H,V2P16C,UG,REW46,5.5



TE Part #DT13-12PC-B016
HDR, 12P, GRN, RA, ENH KEY, NI/CU, C



TE Part #556136-2
CONT,AMPINNRGY WTW,LS PC,10-12



TE Part #2029451-1
06P UMNL SOK HDR ASSY W/O DRNS

Documents

Product Drawings

TERMI-BLOK HEADER,ASSY90 4P.

English

CAD Files

Customer View Model

ENG_CVM_CVM_282828-4_D1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_282828-4_D1.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_282828-4_D1.3d_igs.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS

English

BUCHANAN PCB TERMINAL BLOCKS

English

1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG

English

Product Specifications

Application Specification

English

Agency Approvals

UL

English