



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	6NOV2015	GY	CW



NOTES:
1. TECHNICAL CHARACTERISTICS:
CONTACT MATERIAL: BRASS
SURFACE PLATING:
SILVER PLATING: $\geq 2\mu\text{m}$
GOLD PLATING: $\geq 0.75\mu\text{m}$
WIRE RANGE: $0.08\text{mm}^2\text{-}0.52\text{mm}^2$ (AWG28~AWG20)
OPERATION TEMPERATURE: $-40^\circ\text{C}\sim+125^\circ\text{C}$

注释:
1. 技术参数:
公针材料: 黄铜
表面电镀:
镀银: $\geq 2\mu\text{m}$
镀金: $\geq 0.75\mu\text{m}$
接线范围: $0.08\text{mm}^2\text{-}0.52\text{mm}^2$ (AWG28~AWG20)
工作温度: $-40^\circ\text{C}\sim+125^\circ\text{C}$

-	PART NUMBER AFTER PLATING				Ø d	WIRE GAUGE		STRIPPING LENGTH (mm)	
	SILVER PLATING		GOLD PLATING			MM ²	AWG		
PIN CONTACT	CAF-08	T2070002008-001	DAF-08	T2070012008-001	0.7	0.08-0.21	28-24	4.0	
	CAF-13	T2070002013-001	DAF-13	T2070012013-001	0.9	0.13-0.33	26-22		
	CAF-33	T2070002033-001	DAF-33	T2070012033-001	1.12	0.33-0.52	22-20		
		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Gino.Yao 07AUG2015	 TE Connectivity				
				CHK Chris.Wang 07AUG2015					
		DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-	APVD Xiang.Xu 07AUG2015	NAME			
					PRODUCT SPEC 108-137141	CAF/DAF D-SUB SOCKET CONTACT -			
					APPLICATION SPEC 114-137141				
					MATERIAL - -		FINISH - -	WEIGHT -	SIZE A3
				Customer Drawing			SCALE 6:1	SHEET 1 OF 1	REV A