




Switches > Slide Switches



Contact Current Rating: **.4 A**

Configuration (Pole-Throw): **Single Pole - Double Throw**

Product Orientation: **Right Angle**

Contact Base Material: **Copper Alloy**

Number of Actuators: **Dual**

Features

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Dimensions

Product Width	9.14 mm[.36 in]
Product Length	10.2 mm[.402 in]
Actuator Length	2.7 mm[.106 in]

Termination Features

Termination Post & Tail Length	3.3 mm[.13 in]
Termination Method to PCB	Through Hole - Solder

Body Features

Actuator Orientation	Side
Actuator Travel	3 mm[.118 in]
Product Orientation	Right Angle
Actuator Profile	Extended
Actuator Material	Polyester



Actuator Color	Black
----------------	-------

Configuration Features

Terminals Connected	1-2, 4-5
Configuration (Pole-Throw)	Single Pole - Double Throw
Number of Actuators	Dual
Number of Positions	2
Operating Function	On Off On

Electrical Characteristics

Contact Current Rating	.4 A
Operating Voltage	20 VDC

Contact Features

Contact Base Material	Copper Alloy
Switch Contact Plating Material	Gold

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products




will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

			
TE Part # 1-1437579-3 TSS11EG1RA=SWITCH SLIDE RA TER	TE Part # 1571982-3 TSS11EG1PC04=SLIDE SWITCH SPDT	TE Part # 1571984-1 TSS11DGRA04=SLIDE SWITCH SPDT	TE Part # 1571985-2 TSS11EG1RA04=SLIDE SWITCH SPDT

Customers Also Bought

			
TE Part #36151 PIDG R 22-16 COMM 22-18 MIL 6	TE Part #4-640441-2 12P MTA100 CONN ASSY WHT	TE Part #640456-5 05P MTA100 HDR ASSY F/L SQ STR	TE Part #554954-2 PLUG KIT,50 POSN,SCR LK, SHLD

	
TE Part #5207719-3 KIT SCREWLOCK FEMALE CLEAR ZIN	TE Part #1-480283-0 08P CMNL PLUG HSG M/M NATL

Documents

Product Drawings

TSD21EEGRA04=SLIDE SWITCH

English

CAD Files

Customer View Model

ENG_CVM_CVM_1825014-2_A.3d_igs.zip

English

Customer View Model



[ENG_CVM_CVM_1825014-2_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1825014-2_A.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_1825014-2_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1825014-2_O.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1825014-2_O.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.