




TE Internal #: 5787617-5  
A, 2.0, Standard Profile, Receptacle, 2 Port, Top, Right Angle, Box & Tray / Tray, Through Hole - Solder, Cable-to-Board, 8 Position, USB Connectors  
[View on TE.com >](#)

Connectors > Audio & Video Connectors > USB Connectors



USB Adapter Type: **A**  
USB Version: **2.0**  
Connector Profile: **Standard**  
Connector & Housing Type: **Receptacle**  
Number of Ports: **2**

Features

Industry Standards

Industry Standard	USB 2.0
-------------------	---------

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
-----------------------------	------------------

Contact Features

Contact Mating Area Plating Material	Gold or Gold Flash over Palladium Nickel
Contact Mating Area Plating Material Thickness	.76 µm[29.92 µin]
Contact Current Rating (Max)	1 A

Termination Features

Termination Post & Tail Length	2.29 mm[.09 in]
Termination Method to PCB	Through Hole - Solder

Packaging Features

Packaging Quantity	88
Packaging Method	Tray, Box & Tray

Housing Features



Housing Color	Black
Housing Material	Thermoplastic
Body Orientation	Right Angle
Centerline (Pitch)	2 mm, 2.5 mm[.098 in][.078 in]

Mechanical Attachment

Locking Feature	Without
PCB Mount Location	Top
PCB Mount Retention Type	Boardlock
Connector Mounting Type	Board Mount

Body Features

Shell Plating Material	Tin
Shell Plating Finish	Bright
Connector Profile	Standard

Product Type Features

USB Adapter Type	A
USB Version	2.0
Connector & Housing Type	Receptacle
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board
USB Connector Type	USB 2.0 Type-A

Configuration Features

Number of Ports	2
Number of Positions	8

Usage Conditions

Soldering Temperature (Max)	260 °C[500 °F]
Mating Cycles (Max)	1500
Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 1487599-1  
USB, A-BLUNT,28/28,BLK,0.83M



TE Part # 1487591-1  
USB, A-BLUNT,28/28,WHT,0.83M



TE Part # 1929690-1  
USB CABLE, USB A to Mini USB,Blue



TE Part # 1827525-1  
MECHATROLINK II CONNECTOR KIT





TE Part # 1-1734028-1  
Std USB, Type A, Plug, Natural



TE Part # 1487593-1  
USB, A-BLUNT,28/24,WHT,2.0M



TE Part # 1734028-1  
Std USB Type A, Plug, Natural



TE Part # 1487600-1  
USB, A-BLUNT,28/26,BLK,1.0M



TE Part # 1496476-1  
STD USB-A TO MINI-B ASSY, 1M



TE Part # 1-1734028-3  
Std USB, Type A, Plug



TE Part # 1-2199298-2  
8P,DIP SKT,300 CL,LDR,PB FREE

Customers Also Bought



TE Part #8-1419128-1  
OJ-SH-105LMH,000




TE Part #5-1415535-1  
PE034024




TE Part #216604-6  
2X 6P HV190FEDERLEI



TE Part #2329013-2  
LUMAWISE 40MM DIA DOME SMOKE GRAY TALL



TE Part #4-215911-0  
AMP LATCH, L.P.



TE Part #2-1437565-2  
FSM2JART=ON T/R




TE Part #5536507-4  
2MM FB,ASY,192,SIG,REC,SL,2.73



TE Part #2-1579008-1  
EXTRACTION TOOL



TE Part #1-6457567-4  
ASSY,LC DUP, W/O FLNG AQUA



TE Part #1-926554-1  
HYLSBLOCK ECONOSEAL

Documents



Product Drawings

RECP ASSY, R/A, STACKED, THRU-HOLE, USB,

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_5787617-5\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_5787617-5\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_5787617-5\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English