




Terminals & Splices > Spade Terminals



Spade Terminal Type: **Spade Tongue Terminal**

Wire Size: **509 – 3260 CMA**

Stud Size: **#8, M4**

Features

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Electrical Characteristics

Voltage Rating	600 V
----------------	-------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Body Features

Product Weight	2.116 g
Insulation Sleeve Color	Red
Stripe Color	Red

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Product Type Features

Stud Size	#8, M4
Sealable	No



Wire Insulation Support Retention Type	Insulation Support
--	--------------------

Contact Features

Spade Terminal Type	Spade Tongue Terminal
Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Dimensions

Wire Size	509 – 3260 CMA
Stud Diameter	4.3 mm[.171 in]
Tongue Thickness	.79 mm[.031 in]
Product Length	20.96 mm[.825 in]
Compatible Insulation Diameter (Max)	3.6 mm[.141 in]
Compatible Insulation Diameter Range	2.7 – 3.6 mm[.106 – .142 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 169404
CERTI-LOK DIE



TE Part # 1-1377173-9
SMP 0-0165008-0



TE Part # 47806-2
DIES PIDG 22-16 DIE SET



TE Part # 58423-1
DIE, RBY IS9252



TE Part # 47386
DAHT PG PIDG 26-16 ASSY



TE Part # 58433-3
PRO CR ASSY, RBY IS9252




TE Part # 169400
CERTI-LOK FRAME W/O DIES

Also in the Series | PLASTI-GRIP




Compression Connectors(3)



Crimp Wire Pins, Tabs & Ferrules(20)



Ring Terminals(310)



Spade Terminals(159)



Splices(45)

Customers Also Bought



TE Part #829261-6
HD FEMALE SCREWLOCK




TE Part #4-1601140-1
053-001-000=LEADLOK2,SMZ



TE Part #66461-2
SKT,.062 DIA,.025 SQ POST,LP



TE Part #7-1625890-2
2W SM M/OX 5% 8K2



TE Part #2317655-4
AV25 DPL 3A NO LED FL




TE Part #3-2176362-0
RQ 0402 80R6 0.1% 10PPM 5K RL




TE Part #3-1623931-4
CFR25 5% 470R



TE Part #1601237-1
WIRE2WIRE,FINE,SMZ



TE Part #1601196-1
WIRE2BLADE,HIGH CARRIER,STD,SMZ



TE Part #844890-1
TUBE, DIVIDER

Documents

Product Drawings

PLASTI-GRIP, SPADE 22-16 8

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_165008_J.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_165008_J.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_165008_J.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_165008_C2.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_165008_C2.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_165008_C2.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English