




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**
PCB Mount Orientation: **Vertical**
Connector System: **Wire-to-Board**
Number of Positions: **6**
Number of Rows: **2**

Features

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Dimensions

Row-to-Row Spacing	6.35 mm[.25 in]
Connector Width	13.97 mm[.55 in]
PCB Thickness (Recommended)	3.18 mm[.125 in]
Connector Height	13.97 mm[.55 in]
Connector Length	20.32 mm[.8 in]
Profile Height from PCB	14.73 mm[.58 in]

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Industry Standards

Compatible With Agency/Standards Products	UL, VDE
UL Rating	Recognized



Compatible With Approved Standards Products	UL E28476
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Mechanical Attachment

Panel Mount Feature	Without
Mating Retention Type	Locking Tab
Mating Retention	With
Mating Alignment Type	Polarization
PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	With

Termination Features

Termination Post & Tail Diameter	1.57 mm[.062 in]
Termination Post & Tail Length	5.09 mm[.2 in]
Termination Method to PCB	Through Hole - Solder

Contact Features

Contact Underplating Material	Nickel
Mating Pin Diameter	2.2 mm[.087 in]
Contact Underplating Material Thickness	1.27 – 1.79 µm[50 – 70 µin]
Contact Size	2.2mm
Contact Mating Area Plating Material Thickness	3.81 – 5.08 µm[150 – 200 µin]
PCB Contact Termination Area Plating Material Thickness	3.81 – 5.08 µm[150 – 200 µin]
Contact Shape & Form	Round
Contact Layout	Matrix
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Pre-Tin
Contact Mating Area Plating Material	Pre-Tin
Contact Type	Pin
Contact Current Rating (Max)	12 A



Housing Features

Mating Entry Location	Top
Housing Material	Nylon
Centerline (Pitch)	6.35 mm[.25 in]

Configuration Features

Number of Columns	3
Number of Loaded Positions	6
Number of Power Positions	6
Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Vertical
Number of Positions	6
Number of Rows	2

Product Type Features

Mixed & Hybrid Header	No
Connector Shape	Rectangular
PCB Connector Assembly Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Body Features

Primary Product Color	Natural
-----------------------	---------

Operation/Application

Circuit Application	Power
---------------------	-------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1586860-1 06P UMNL CAP HSG, GW	 TE Part # 8-794536-1 06P UMNL CAP HSG 150C BLK, SPE	 TE Part # 770020-1 06P UMNLI IN-LNE PLUG HSG KIT	 TE Part # 926682-4 6P UN-MNL AUFN-GEH
 TE Part # 1969881-1 06P UMNL CAP HSG, P/M, GW V0	 TE Part # 1969814-1 06P UMNL PIN HDR ASSY, PIN V0 GW	 TE Part # 643749-1 06P UMNL HDR ASSY W/O DRNS	 TE Part # 350848-6 06P UMNL PLUG TEST ASSY 94V0



TE Part # 1586090-3
06P UMNL PINHDR W/O DR HOLE LF



TE Part # 643253-1
06P UMNL ASSY MOD HSG VO



TE Part # 350715-1
06P UMNL PLUG HSG




TE Part # 1969830-1
6P UMNL SKT ASSY GW




TE Part # 1969811-1
06P UMNL SKT HDR ASSY, SCKT V0 GW




TE Part # 2029367-1
06P UMNL-II TW-N-LK-CAP FRONT



TE Part # 2029369-1
06P UMNL-II REAR, TW-N-LK-CAP



TE Part # 641956-2
6P UMNL HDR HSG POL



TE Part # 1-640721-0
06P UMNL STR/REL & INSRT NATL



TE Part # 1586887-1
06P UMNL CAP HSG, P/M, GW



TE Part # 640715-1
06P UMNL STR/REL



TE Part # 794536-1
06P UMNL CAP HSG 150C BLK

Also in the Series | Universal MATE-N-LOK



Circular Power Connectors(2)



Connector Contacts(209)



Connector Hardware(12)



Power Contacts(209)



Rectangular Power Connectors(370)



Standard Circular Connectors(1)

Customers Also Bought



TE Part #2309413-1
DDR4 SODIMM 260P 9.2H STD



TE Part #2-1473562-4
RITS CONN. PLUG ASSY 4P BLUE



TE Part #5-103634-4
05 MTE HDR SRRA LATCH.100CL LF




TE Part #170204-2
EIS CONTACT



TE Part #207583-6
MMATE PIN HDR ASSY,6P LF



TE Part #1-1674231-1
2.5MM PITCH BATTERY REC ASSEMBLY DIP TYP




TE Part #1571986-8
A101J1AQ004=SGL POLE,ROCKER



TE Part #2344656-4
WLAN DUAL BAND ANTENNA FPC V 200mm



TE Part #2-1746741-4
RITS CONN. SOCKET ASSY 4P BLUE



Documents

Product Drawings

06P UMNL PIN HDR ASSY 94VO

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_350732-1_V.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_350732-1_V.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_350732-1_V.3d_stp.zip

English

Customer View Model

ENG_CVM_350732-1_R.3d_igs.zip

English



Customer View Model

[ENG_CVM_350732-1_R.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_350732-1_R.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[UL](#)

English