




PIDG

TE Internal #: 324075
Closed Ring Tongue Terminal, 26 – 22 AWG, #10 Stud, 5 mm [.197 in] Stud Diameter, Closed Barrel, Straight, Tin Plating, Partially Insulated, PIDG

[View on TE.com >](#)

Terminals & Splices > Ring Terminals > PIDG Ring Tongue Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 202 – 810 CMA

Stud Size: #10

[All PIDG Ring Tongue Terminals \(410\)](#)

Features

Configuration Features

| | |
|-----------------|---|
| Number of Holes | 1 |
|-----------------|---|

Body Features

| | |
|----------------|--------|
| Product Weight | .287 g |
|----------------|--------|

Mechanical Attachment

| | |
|-------------------------|------|
| Wire Insulation Support | With |
|-------------------------|------|

Electrical Characteristics

| | |
|----------------|-------|
| Voltage Rating | 300 V |
|----------------|-------|

Industry Standards

| | |
|-------------------------------|----|
| Government Qualified Terminal | No |
|-------------------------------|----|

Packaging Features

| | |
|--------------------|-------------|
| Packaging Quantity | 1000 |
| Packaging Method | Loose Piece |

Product Type Features



| | |
|--|-----------------------------|
| Ring Terminal Product Type | Closed Ring Tongue Terminal |
| Stud Size | #10 |
| Sealable | No |
| Wire Insulation Support Retention Type | Insulation Support |

Contact Features

| | |
|---------------------------|----------|
| Barrel Type | Closed |
| Terminal Orientation | Straight |
| Terminal Plating Material | Tin |

Dimensions

| | |
|--------------------------------------|--------------------------------|
| Wire Size | 202 – 810 CMA |
| Stud Diameter | 5 mm [.197 in] |
| Tongue Thickness | .79 mm [.031 in] |
| Product Length | 18.8 mm [.74 in] |
| Compatible Insulation Diameter (Max) | 2.08 mm [.082 in] |
| Compatible Insulation Diameter Range | 1.27 – 2.08 mm [.05 – .082 in] |

Usage Conditions

| | |
|-------------------|---------------------|
| Insulation Option | Partially Insulated |
|-------------------|---------------------|

Operation/Application

| | |
|---------------------------------------|--------|
| Compatible With Wire Base Material | Copper |
| Compatible With Wire Plating Material | Tin |

Other

| | |
|--------------------|-----------|
| EU RoHS Compliance | Compliant |
| EU ELV Compliance | Compliant |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC |



| | |
|---------------------------|---|
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 59275
T-HEAD PIDG PG SH 26-20 ASSY

TE Part # 69344
PIDG 26-22 DIE SET

TE Part # 46121
DAHT PG PIDG 26-22 ASSY

Also in the Series | PIDG

Compression Connectors(17)

Crimp Wire Pins, Tabs & Ferrules(41)

Knife Disconnects(11)

Quick Disconnects(38)

Ring Terminals(588)


Spade Terminals(228)

Special Purpose Terminals(1)


Splices(41)




Customers Also Bought




TE Part #52943
TERMINAL,PIDG SPR SPD 12-10 10




TE Part #CAT-104MTA-NGPMR
Nylon Gold Plated Receptacle: 2.54 mm, with Mating Alignment, MTA 100




TE Part #350570-2
UMNL SOK 24-18 AUBR




TE Part #52464
TERMINAL,PG SPR SPD 16-14 8




TE Part #171505-1
PIDG RING UL.CSA(22-18)




TE Part #234461-000
222D132-25/225-0



TE Part #292168-2
CT P/HDR ASSY 2P H W/O KINK TU



TE Part #2174219-1
Push-Pull 7P Plug PS S-Cup Cont KIT/N



TE Part #1520230-2
7402K4=20 AMP TOGGLE

Documents

Product Drawings
TERMINAL,PIDG R 26-22 10
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_324075_F.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_324075_F.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_324075_F.3d_stp.zip
English
3D PDF



- English
- Customer View Model
- ENG_CVM_324075_G.2d_dxf.zip
- English
- Customer View Model
- ENG_CVM_324075_G.3d_igs.zip
- English
- Customer View Model
- ENG_CVM_324075_G.3d_stp.zip
- English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

- Datasheets & Catalog Pages
- PIDG Terminals and Splices Quick Reference Guide
- English
- PIDG TERMINALS & SPLICES Quick Reference Guide
- English

- Agency Approvals
- CSA Certificate
- English