



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**

Wire Size: **1021 – 2048 CMA**

Mating Tab Width: **2.8 mm [.11 in]**

Features

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Mating Retention Type	Locking Lance
-----------------------	---------------

Packaging Features

Packaging Quantity	4000
Packaging Method	Reel

Dimensions

Product Length	22.5 mm[.885 in]
Compatible Insulation Diameter Range	1.4 – 2.3 mm[.055 – .09 in]
Wire Size	1021 – 2048 CMA

Contact Features

Quick Disconnect Terminal Type	Tab
--------------------------------	-----



Mating Tab Width	2.8 mm[.11 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Copper Zinc Alloy
Terminal Plating Material	Silver
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2151379-1
OCEAN_2.0_Applicator-S-080F110OV-RSM

TE Part # 2151379-2
OCEAN_2.0_Applicator-S-080F110OV-RSA

TE Part # CAT-T4827-CH8172
Timer Connector Housing

TE Part # 1-1579007-4
EXTRACTION TOOL

TE Part # 4-1579007-3
EXTRACTION TOOL KIT

TE Part # 7-2151379-7
OCEAN_2.0_SPARE_PART_KIT-080F110OV

TE Part # 2305570-1
Strip Terminal Cutter-Side Feed-No Crimp

Also in the Series | FASTIN-FASTON 110

Automotive Housings(6)

Automotive Terminals(5)

Crimp Terminal Housings(34)


Insertion & Extraction Tools(3)

Quick Disconnects(83)

Customers Also Bought



TE Part #CAT-T4827-CH8172
Timer Connector Housing



TE Part #160451-2
FF 250 TAB 18-14AWG TPPB LP



TE Part #1-968976-9
MCP2.8 BU-GEH 3P



TE Part #1-1703498-2
2POS, MCON 1.2 LL TAB SEALED COD A



TE Part #1718762-1
MCON 1.2 LL TAB SWS SN



TE Part #EC0179-000
05811101



TE Part #927783-3
JPT REC 2.8 Contact SRC Sn (LP)



TE Part #963827-3
FF STECKHUELSE 9,5

Documents

Product Drawings

FF 110 TAB 0.5-1 MM2 .080 F SSP CUZN30

English

FF 110 TAB 0.5-1 MM2 .080 F SSP CUZN30

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_928930-1_P.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_928930-1_P.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_928930-1_P.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

German

Application Specification

English