



Connectors > Power Connectors > Circular Power > Circular Power Connectors



Number of Positions: 4
Connector Product Type: **Housing**
Operating Voltage: 250 VDC
Wire Size: .0509 – .823 mm²

Features

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Mechanical Attachment

Mating Retention Type	Threaded Coupling
Thread Size	1/2-20 UNF-2A
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)
Mating Retention	With
Panel Mount Feature	Without

Dimensions

Compatible Insulation Diameter Range	1.5 – 2.39 mm[.059 – .11 in]
Wire Size	.0509 – .823 mm ²

Product Type Features

Connector Seal & Plug Type	Wire Entry Seal
----------------------------	-----------------



Connector Product Type	Housing
Connector System	Wire-to-Wire
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Plug
Circular Connector Shell Type	All Plastic

Configuration Features

Number of Positions	4
Number of Power Positions	0
Number of Signal Positions	4

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Reverse Gender	No
Contact Type	Socket
Contact Current Rating (Max)	7.5 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Housing Features

Housing Color	Black
Housing Material	Thermoplastic
Circular Connector Shell Size	8

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Fluid Resistance	Immersion

Operation/Application

Circuit Application	Power & Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Other

--	--



EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 770903-1
MINI UMNL PIN 22-18 AWG SN




TE Part # 770904-6
MINI UMNL SOK CONT 22-18AWG AU




TE Part # 1-770988-0
MINI UMNL SOK 22-18AWG AU



TE Part # 770987-1
MINI UMNL PIN 22-18AWG SN LP




TE Part # 1-770903-1
MINI UMNL PIN 22-18 AWG AU LF



TE Part # 1-770834-0
MINI UMNL SOK AU LF



TE Part # 770901-1
MINI UMNL PIN 26-22 AWG SN



TE Part # 770987-3
MINI UMNL PIN 22-18 AWG AU LP



TE Part # 770835-1
MINI UMNL PIN SN



TE Part # 770904-1
MINI UMNL SOK 22-18 AWG SN




TE Part # 770986-1
MINI UMNL SOK 26-22AWG SN LP



TE Part # 770834-1
MINI UMNL SOCKET SN



TE Part # 1445421-1
REC,8-4,FLNG MT,SM INS,STD KEY




TE Part # 1-770903-0
MINI UMNL PIN 22-18 AWG AU




TE Part # 1-794058-0
MINI UMNL SOK L/P LF



TE Part # 1-770986-0
MINI UMNL SOK 26-22AWG AU LP



TE Part # 1-770901-0
MINI UMNL PIN 26-22 AWG AU LF



TE Part # 1-770987-0
MINI UMNL PIN 22-18 AWG AU LP



TE Part # 770902-6
MINI UMNL SOK 26-22 AWG AU



TE Part # 770834-4
MINI UMNL SOCKET PHBR

Also in the Series | AMP CPC



Connector Backshells(1)



Connector Caps & Covers(16)



Connector Contacts(6)



Connector Seals & Cavity Plugs(35)



Connector Strain Relief(60)



Insertion & Extraction Tools(1)



Power Contacts(6)

Customers Also Bought




TE Part #207516-5
HDP-20,RCPT,SIZE 3, 25 POSN,CL




TE Part #4-6609107-5
PS0XSXA=C1099



TE Part #787171-5
50 50SR R/A RCPT ASSY,REDESIGN



TE Part #1977884-1
SLD CPC PLUG ASSY,13-9,STD SEX,UV RESIS



TE Part #796094-2
SLD CPC PLUG ASY,11-4,STD SEX




TE Part #1825289-1
MHS22204=DPDT SL SW VERT AG



TE Part #1445535-3
PLUG,8-2,LG INS,STD KEY



TE Part #1445538-3
REC,8-2,FLNG MT,LG INS,STD KEY



TE Part #2-87631-1
26 MODIV HSG COMP DR .100 POL



TE Part #7-1393132-5
P40P42D12P1-24=CONTACTORS-

Documents

Product Drawings
PLUG,8-4,LG INS,STD KEY
English

CAD Files
Customer View Model
ENG_CVM_CVM_1445390-3_C2.3d_igs.zip
English
Customer View Model



[ENG_CVM_CVM_1445390-3_C2.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1445390-3_C2.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1773902-9_CPC_Catalog](#)

English

[1-1773902-9_CPC_Catalog](#)

[1-1773902-9_CPC_Catalog](#)

German

[1-1773902-9_CPC_Catalog](#)

Japanese

[AMP Circular Connectors for Commercial Signal & Power Applications Continued](#)

English

Product Specifications

[Application Specification](#)

English

[Application Specification](#)

English