

HV M10/1 - High-current connector

3049408

<https://www.phoenixcontact.com/us/products/3049408>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



High-current connector, nom. voltage: 1000 V, nominal current: 269 A, number of connections: 1, connection method: Bolt connection, Rated cross section: 120 mm², mounting type: NS 35/7,5, NS 35/15, color: gray

Your advantages

- Comprehensive, supplementary accessories
- For connecting up to four conductors

Commercial data

Item number	3049408
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE42
Product key	BE4211
Catalog page	Page 397 (C-1-2019)
GTIN	4046356184076
Weight per piece (including packing)	98.35 g
Weight per piece (excluding packing)	91.95 g
Customs tariff number	85369010
Country of origin	CN

HV M10/1 - High-current connector

3049408

<https://www.phoenixcontact.com/us/products/3049408>



Technical data

Product properties

Product type	Bolt connection terminal block
Product family	HV
Pitch	34 mm
Number of connections	1
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	8.68 W

Connection data

Number of connections per level	1
Nominal cross section	120 mm ²
Stripping length	The stripping length depends on the specification provided by the cable lug manufacturer.
Connection in acc. with standard	IEC 60947-7-1
Nominal current	269 A
Maximum load current	269 A (with 120 mm ² conductor cross section)
Nominal voltage	1000 V
Nominal cross section	120 mm ²

Cable lug connection DIN 46234:1980-03

Connection in acc. with standard	DIN 46234:1980-03
Cross section	6 mm ² ... 120 mm ²
Cross section range AWG	8 ... 250 kcmil (converted acc. to IEC)
Hole diameter	10.5 mm
Width	24 mm
Bolt diameter	10 mm
Screw thread	M10
Tightening torque	10 ... 20 Nm
Connection in acc. with standard	DIN 46235:1983-07
Cross section	16 mm ² ... 95 mm ²
Cross section range AWG	4 ... 250 kcmil (converted acc. to IEC)
Hole diameter	10.5 mm
Width	32 mm
Bolt diameter	10 mm
Screw thread	M10

HV M10/1 - High-current connector

3049408

<https://www.phoenixcontact.com/us/products/3049408>



Tightening torque	10 ... 20 Nm
Connection in acc. with standard	DIN 46237:1970-07
Cross section	... 6 mm ²
Cross section range AWG	... 8 (converted acc. to IEC)
Hole diameter	10.5 mm
Width	18 mm
Bolt diameter	10 mm
Screw thread	M10
Tightening torque	10 ... 20 Nm

Dimensions

Width	32 mm
End cover width	2 mm
Height	64 mm
Depth	74.6 mm
Depth on NS 35/7,5	75.3 mm
Depth on NS 35/15	82.8 mm
Bolt length	41 mm
Pitch	34 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Electrical tests

Surge voltage test	
Test voltage setpoint	9.8 kV
Result	Test passed

Temperature-rise test	
Requirement temperature-rise test	Increase in temperature ≤ 45 K
Result	Test passed
Short-time withstand current 120 mm ²	14.4 kA

HV M10/1 - High-current connector

3049408

<https://www.phoenixcontact.com/us/products/3049408>



Result	Test passed
Power-frequency withstand voltage	
Test voltage setpoint	2.2 kV
Result	Test passed

Mechanical properties

Mechanical data	
Open side panel	No

Mechanical tests

Mechanical strength	
Result	Test passed
Attachment on the carrier	
DIN rail/fixing support	NS 35
Test force setpoint	15 N
Result	Test passed

Environmental and real-life conditions

Needle-flame test	
Time of exposure	30 s
Result	Test passed

Oscillation/broadband noise	
Specification	DIN EN 50155 (VDE 0115-200):2018-05
Spectrum	Service life test category 1, class B, body mounted
Frequency	$f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$
ASD level	$0.964 \text{ (m/s}^2\text{)}^2/\text{Hz}$
Acceleration	5.72g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Result	Test passed

Shocks	
Specification	DIN EN 50155 (VDE 0115-200):2018-05
Pulse shape	Half-sine
Acceleration	5g
Shock duration	30 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Result	Test passed

Ambient conditions	
Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating)

HV M10/1 - High-current connector

3049408

<https://www.phoenixcontact.com/us/products/3049408>



	for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1
----------------------------------	---------------

Mounting

Mounting type	NS 35/7,5
	NS 35/15

HV M10/1 - High-current connector

3049408

<https://www.phoenixcontact.com/us/products/3049408>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3049408>



CSA

Approval ID: 13631



cUL Recognized

Approval ID: FILE E 60425

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Use group C	1000 V	269 A	-	-



EAC

Approval ID: RU C-DE.BL08.B.00540



CSA

Approval ID: 13631

HV M10/1 - High-current connector

3049408

<https://www.phoenixcontact.com/us/products/3049408>



Classifications

ECLASS

ECLASS-11.0	27141120
ECLASS-13.0	27250101

ETIM

ETIM 9.0	EC000897
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HV M10/1 - High-current connector

3049408

<https://www.phoenixcontact.com/us/products/3049408>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com