




Triad 01 Cable Plug, Triad 01 Solder

TE Internal #: 3-1437719-6

5 Position Circular Connector, Cable-to-Cable, Sealable, Wire & Cable, Signal, Reverse Gender, Nickel, CuZn, PBT, Triad 01 Cable Plug

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors



Number of Positions: 5

Connector System: **Cable-to-Cable**

Sealable: **Yes**

Connector & Contact Terminates To: **Wire & Cable**

Contact Current Rating (Max): **3 A**

Features

Electrical Characteristics

Operating Voltage	60 VAC
-------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Packaging Features

Packaging Quantity	25
--------------------	----

Dimensions

Compatible Insulation Diameter Range	5 mm
Assembly Length	38 mm
Wire Size	24 AWG

Body Features

Environmental Protection Type	Sealed
Environmental Protection	With
Shell Plating Material	Nickel



Shell Base Material	CuZn
Circular Connector Insulation Material Type	PBT
Hermetically Sealed	No

Product Type Features

Prewired	Yes
Connector Product Type	Connector Assembly
Connector System	Cable-to-Cable
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Circular Connector Type	Receptacle
Shell Type	Metal

Configuration Features

Number of Positions	5
Number of Power Positions	0
Number of Signal Positions	5
Contacts Preloaded	Yes

Contact Features

Contact Current Rating (Max)	3 A
Reverse Gender	Yes
Contact Layout Arrangement	Circular
Circular Connector Contact Type	Socket

Mechanical Attachment

Mating Retention	With
------------------	------

Usage Conditions

Operating Temperature Range	-40 – 80 °C[-40 – 176 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
Shielded	No

Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (3% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Hand solderable with lead free solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5-1437719-1
T01-0560-P05-MALE REC PANEL-PCB MOUNT RA



TE Part # 2-1437719-1
T01-0550-P05-MALE PLUG CONNECTOR SOLDER



TE Part # 6-1437719-5
T01-0570-P05-MALE REC PANEL-PCB STRAIGHT



TE Part # 8-1437719-7
T01-0580-P05-MALE REC PANEL MOUNT SOLDER

Also in the Series | Triad 01 Cable Plug




Standard Circular Connectors(10)

Also in the Series | Triad 01 Solder



Standard Circular Connectors(10)

Customers Also Bought



TE Part #1-1437719-5
T01-0550-P03-MALE PLUG
CONNECTOR SOLDER



TE Part #9-1437719-9
T01-0580-S04-FEMALE REC PANEL
MNT SOLDER



TE Part #2-1437719-4
T01-0550-P07-MALE PULG
CONNECTOR SOLDER



TE Part #8-1437719-4
T01-0580-P04-MALE REC PANEL
MOUNT SOLDER



TE Part #EC0050-000
05801910



TE Part #EC0077-000
05801937



TE Part #EC0054-000
05801914



TE Part #1437720-6
T01-0580-S07-FEMALE REC PANEL
MNT SOLDER



TE Part #EC0052-000
05801912



TE Part #EC0076-000
05801936



Documents

Product Drawings

T01-0550-S05-FEMALE PLUG CONNECTOR SOLDE

English

T01-0550-S05-FEMALE PLUG CONNECTOR SOLDE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-1437719-6_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-1437719-6_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-1437719-6_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M8 / M12 Connector System Catalog

English

Product Specifications

Product Specification

English