



Connectors > Circular Connectors > Standard Circular Connectors



Number of Positions: 6

Connector System: **Wire-to-Wire**

Connector & Contact Terminates To: **Wire & Cable**

Circular Connector Contact Type: **Pin**

EU RoHS Compliance: **Compliant**

Features

Configuration Features

Number of Positions	6
---------------------	---

Product Type Features

Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Contact Features

Circular Connector Contact Type	Pin
---------------------------------	-----

Other

EU RoHS Compliance	Compliant
--------------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUN 2018 (191) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC




Free

Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #2213223-1
NECTOR M PANEL MOUNT SEAL




TE Part #2213351-1
NECTOR M SEAL/CABLE CLAMP ASSEMBLY, 14MM




TE Part #2213226-3
NECTOR M POSITIONER HOUSING




TE Part #2213229-2
NECTOR M RING NUT, 5/6/7P, 14-17MM




TE Part #2213351-2
NECTOR M SEAL/CABLE CLAMP ASSEMBLY, 17MM




TE Part #2213393-1
NECTOR M PIN HOUSING, PANEL, 6P, CODE A




TE Part #2213239-1
NECTOR M SKT HSG ASSY, FH, 6P, CODE A



TE Part #1-2213266-2
NECTOR M PIN, CRIMP, 16-18 AWG



TE Part #2213430-1
NECTOR M 5/6/7P SCREW NUT, PANEL MOUNT



TE Part #2213262-1
NECTOR M SKT HSG ASSY, PM, 6P CODE A

Documents

- CAD Files
- 3D PDF



3D

Customer View Model

[ENG_CVM_CVM_2213241-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2213241-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2213241-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English