




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **404 – 643 CMA**

Mating Tab Width: **2.8 mm [.11 in]**

Features

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Packaging Features

Packaging Quantity	20000
Packaging Method	Reel

Dimensions

Product Length	16.13 mm[.635 in]
Compatible Insulation Diameter Range	1.01 – 1.52 mm[.04 – .06 in]



Terminal Material Thickness	.25 mm[.01 in]
Wire Size	404 – 643 CMA

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	2.8 mm[.11 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as



EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



KIT

REPRESENTATION ONLY

TE Part # 7-2150043-7
[OCEAN_2.0_SPARE_PART_KIT-062F070O](#)



TE Part # 2150043-2
[OCEAN_2.0_Applicator-S-062F070O-RSA](#)




TE Part # 2063846-1
[CCII 110 FASTON REC 24-18 ASSY](#)



TE Part # 2150043-1
[OCEAN_2.0_Applicator-S-062F070O-RSM](#)

Also in the Series | **FASTON 110**



[Crimp Terminal Housings\(13\)](#)



[Insertion & Extraction Tools\(1\)](#)



[PCB Terminals\(22\)](#)



[Quick Disconnects\(168\)](#)

Customers Also Bought



TE Part #1-2176343-2
[CRGCQ 1206 82R 1%](#)



TE Part #1-2176328-4
[CRGP 1206 120R 1%](#)



TE Part #215570-6
[MICRO-MATCH PBC.06P](#)



TE Part #1437720-3
[T01-0580-S05-FEMALE REC PANEL MNT SOLDER](#)



TE Part #3-2176309-9
RP 1E 0.1W 24R9 0.1% 25PPM 1K RL

TE Part #1-215297-4
14P HV100 REC CON. TE, 7.0MM

TE Part #1-968696-3
4POS MQS TAB COD A

TE Part #187752-000
CR-107-LSR

TE Part #140716-2
110 FASTON,REC.,24-22 AWG,PTBR

TE Part #2-2176324-2
SMV 3W 5M6 5%

Documents

Product Drawings

110 FASTON REC 24-22 AWG TPBR

English

CAD Files

Customer View Model

ENG_CVM_CVM_63634-1_D.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_63634-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_63634-1_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

82004 FASTON Terminals (Insulated and Uninsulated) Catalog - FASTON Receptacles Section

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

63634-1

Quick Disconnect Receptacle, 24 – 22 AWG, .2 – .35 mm² Wire, 404 – 643 CMA, 2.8 mm [.11 in] Tab Width, Straight, Brass, Tin Plating, Reel, FASTON 110



English