

## D SUB MIXED MA 30 A CR POWER CONTACT PL3



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 69 282 7422                                                                |
| Specification      | D SUB MIXED MA 30 A CR POWER CONTACT PL3                                      |
| HARTING eCatalogue | <a href="https://harting.com/09692827422">https://harting.com/09692827422</a> |

### Identification

|                            |               |
|----------------------------|---------------|
| Category                   | Contacts      |
| Series                     | D-Sub         |
| Identification             | Mixed         |
| Type of contact            | Crimp contact |
| Description of the contact | Straight      |

### Version

|                       |                   |
|-----------------------|-------------------|
| Termination method    | Crimp termination |
| Termination method    | Crimp termination |
| Gender                | Male              |
| Manufacturing process | Turned contacts   |

### Technical characteristics

|                               |                         |
|-------------------------------|-------------------------|
| Conductor cross-section       | 4 ... 6 mm <sup>2</sup> |
| Conductor cross-section [AWG] | AWG 12 ... AWG 10       |
| Rated current                 | ≤30 A                   |
| Contact resistance            | ≤1 mΩ                   |
| Stripping length              | 7.5 mm                  |
| Limiting temperature          | -55 ... +155 °C         |
| Insertion force               | ≤7 N                    |
| Withdrawal force              | ≈5 N                    |
| Performance level             | 3                       |



**Pushing Performance**  
Since 1945

## Technical characteristics

|               |     |
|---------------|-----|
| Mating cycles | ≥50 |
|---------------|-----|

## Material properties

|                                      |                                                        |
|--------------------------------------|--------------------------------------------------------|
| Material (contacts)                  | Copper alloy                                           |
| Surface (contacts)                   | 0.2 µm Au                                              |
| Material (locking)                   | Copper alloy                                           |
| RoHS                                 | compliant with exemption                               |
| RoHS exemptions                      | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                           | compliant with exemption                               |
| China RoHS                           | 50                                                     |
| REACH Annex XVII substances          | Not contained                                          |
| REACH ANNEX XIV substances           | Not contained                                          |
| REACH SVHC substances                | Yes                                                    |
| REACH SVHC substances                | Lead                                                   |
| ECHA SCIP number                     | ecef7555-f643-4ceb-a337-fc54762297f1                   |
| California Proposition 65 substances | Yes                                                    |
| California Proposition 65 substances | Lead<br>Nickel                                         |

## Commercial data

|                                |                                            |
|--------------------------------|--------------------------------------------|
| Packaging size                 | 100                                        |
| Net weight                     | 2.679 g                                    |
| Country of origin              | Germany                                    |
| European customs tariff number | 85366990                                   |
| GTIN                           | 5713140099470                              |
| ETIM                           | EC000796                                   |
| eCl@ss                         | 27440204 Contact for industrial connectors |