

RN73C1E57K6BTD

✓ ACTIVE

Holsworthy | Holsworthy RN73

TE Internal #: 3-2176263-7

Surface Mount Precision Resistor, Thin Film, 0402, .063 W, 57.6K ohm, .1 %, ±10 ppm/°C, Solder, 2 Terminations, Holsworthy RN73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**  
Element Type: **Thin Film**  
Package Size Code: **0402**  
Power Rating: **.063 W**  
Resistance Value: **57.6K  $\Omega$**

Features

Industry Standards

Moisture Sensitivity Level	1
----------------------------	---

Electrical Characteristics

Operating Voltage	25 V
Power Rating	.063 W
Resistance Value	57.6K $\Omega$
Resistance Class	1k $\Omega$ – 1M $\Omega$
Passive Component Tolerance	.1 %

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film
Package Size Code	0402

Configuration Features

Number of Resistors	1
---------------------	---

Termination Features

--	--



Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.3 mm[.012 in]
Product Length	1 mm[.039 in]
Product Width	.5 mm[.02 in]

Usage Conditions

Temperature Coefficient	±10 ppm/°C
-------------------------	------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 3-2176263-8  
[RN 0402 59K 0.1% 10PPM 5K RL](#)

TE Part # 3-2176263-6  
[RN 0402 56K2 0.1% 10PPM 5K RL](#)

Also in the Series | [Holsworthy RN73](#)

[Surface Mount Resistors\(3641\)](#)

Customers Also Bought

TE Part #5-1879021-1  
[SMW3 12R 5%](#)

TE Part #4-1625971-8  
[HSA25 3R9 5%](#)

TE Part #3-2176364-3  
[RQ 0402 10K 0.1% 10PPM 5K RL](#)

TE Part #3-2176363-6  
[RQ 0402 1K0 0.1% 10PPM 5K RL](#)

TE Part #6-2176363-5  
[RQ 0402 2K0 0.1% 10PPM 5K RL](#)

TE Part #2-2176364-1  
[RQ 0402 7K5 0.1% 10PPM 5K RL](#)

TE Part #YDTS20F19-32SNV001  
[RECP ASSY](#)

TE Part #7-1879132-2  
[RN 0402 49K9 0.1% 10PPM 1K RL](#)

RN73C1E57K6BTD

Surface Mount Precision Resistor, Thin Film, 0402, .063 W, 57.6K ohm, .1 %, ±10 ppm/°C, Solder, 2 Terminations, Holsworthy RN73



TE Part #2367197-6  
1.0mm WTB Side Vertical Type With Latch



TE Part #6-2176455-0  
CPF 0402 453K 0.1% 25ppm 1K RL

Documents

Product Drawings

[RN 0402 57K6 0.1% 10PPM 5K RL](#)

English

Datasheets & Catalog Pages

[High Precision Resistors \(SMD\) - Type RN73 Series - Tyco Electronics Passives](#)

English