




MTA 156

TE Internal #: 3-644662-6

Connector Assembly, Receptacle, Insulation Displacement (IDC),
Wire-to-Board, MTA 156, Standard Rectangular Connectors

[View on TE.com >](#)

Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Connector Assembly**
Connector & Housing Type: **Receptacle**
Mating Alignment: **With**
Mating Alignment Type: **Polarization**
Mating Retention: **With**

Features

Packaging Features

Packaging Quantity	250
Packaging Method	Bag/Box

Dimensions

Product Width	9.02 mm[.355 in]
Product Length	23.77 mm[.936 in]
Connector Height	18.42 mm[.725 in]
Wire Size	22 AWG

Housing Features

Housing Material	Nylon
Housing Color	Red
Centerline (Pitch)	3.96 mm[.156 in]

Configuration Features

Number of Cavities	6
Contacts Preloaded	Yes



Number of Positions	6
Number of Rows	1

Industry Standards

Compatible With Agency/Standards Products	UL, CSA
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
CSA Rating	LR 7189
UL Flammability Rating	UL 94V-2

Contact Features

Contact Underplating Material	Nickel
Wire Contact Termination Area Plating Material	Tin
Contact Type	Receptacle
Contact Mating Area Plating Material	Gold Flash over Palladium Nickel, Gold
Contact Retention Within Housing	With
Contact Current Rating (Max)	7 A

Mechanical Attachment

Contact Retention Type Within Housing	Locking Lance
Mating Alignment	With
Mating Alignment Type	Polarization
Mating Retention	With
Mating Retention Type	Locking Ramp
Connector Mounting Type	Cable Mount (Free-Hanging)

Product Type Features

Compatible With Discrete Wire Type	Stranded
Connector Product Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Insertion Force Type	Normal
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------



Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Shielded	No
Circuit Application	Signal

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 3-644759-6
06P MTA156 HDR ASSY STR LF




TE Part # 3-641208-6
06P MTA156 HDR ASSY FL ST LF




TE Part # 3-644760-6
06P MTA156 HDR ASSY FL ST LF




TE Part # 640551-6
06P MTA156 COVER




TE Part # 640643-6
06P MTA156 COVER F/T



TE Part # 641208-6
06P MTA156 HDR ASSY FL ST 30AU




TE Part # 643071-6
06P MTA156 FD-THRU COVER




TE Part # 641318-3
06CIR MTA156 R/A HDR ASY W/O#3




TE Part # 58247-3
MTA 156 CRIMP HEAD PRODUCTION
RBBN CABLE



TE Part # 3-641210-6
06P MTA156 HRD FL RA FB 30AU




TE Part # 3-641202-6
06P MTA156 HDR ASSY PL 30AU LF



TE Part # 3-641209-6
06P MTA156 HDR ASSY FL ST LF



TE Part # 58074-1
MTA 50/100/156 MANUAL TOOL
FRAME



TE Part # 3-644761-6
06P MTA156 HDR ASSY R/A F/L LF



TE Part # 58247-2
MTA 156 CRIMP HEAD PRODUCTION
DISCRETE



TE Part # 643067-6
06P MTA156 MOLDED COVER

Also in the Series | **MTA 156**



Connector Caps & Covers(89)



Connector Contacts(4)



Connector Hardware(2)



Power Contacts(3)



Rectangular Power Connectors(331)



Standard Rectangular Connectors(336)



Wire-to-Board Headers & Receptacles (677)

Customers Also Bought



TE Part #211401-1
RECEPT,SZ 13-7,CPC



TE Part #1-206062-4
CABLE CLAMP KIT #11



TE Part #2-1437667-4
4DB-P108-02=4DB ASSEMBLY



TE Part #3-641437-2
02P MTA156 PSTD CONN ASSY RED



TE Part #1-66359-6
III+ PIN,18-14,30AU/FL,STRIP



TE Part #1-66360-4
III+ SKT,18-14,30AU/FL,LP



TE Part #1622796-1
YR1 0.1% 100K



TE Part #36154
PIDG R 22-16 COMM 22-18 MIL 10



TE Part #5748677-1
PLTD PLST CBL CLMP KIT,SZ 1



TE Part #390088-1
BLACK HSG WITH 30AU CONTACT

Documents

Product Drawings

06P MTA156 CONN ASSY 22AWG LF

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-644662-6_J.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_3-644662-6_J.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-644662-6_J.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

Japanese

[Application Specification](#)

English

[MTA 156 Ribbon Cable Connector Assemblies \(English And Spanish\)](#)

English

[MTA 156 Ribbon Cable Connector Assemblies \(English And Spanish\)](#)

Japanese

[Application Specification](#)

English

Agency Approvals

[UL](#)

English