



Connectors > Pluggable IO Connectors & Cages



Form Factor: **QSFP+**
Pluggable I/O Product Type: **Cage Assembly**
Sealable: **Yes**
Circuit Application: **Signal**
Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Post & Tail Length	2.2 mm[.086 in]

Contact Features

PCB Contact Termination Area Plating Material	Tin
---	-----

Dimensions

PCB Thickness (Recommended)	1.45 mm[.057 in]
-----------------------------	------------------

Housing Features

Cage Material	Nickel Silver
---------------	---------------

Body Features

Heat Sink Style	Pin
Heat Sink Finish	Anodized Black
	.165 in
Heat Sink Height Class	PCI

Packaging Features

Packaging Method	Box & Tray
------------------	------------



Configuration Features

Number of Rear EONs per Port Column	2
Number of Ports	4
Port Matrix Configuration	1 x 4

Operation/Application

Pluggable I/O Applications	SFP+ Stacked Belly-to-Belly
Circuit Application	Signal

Product Type Features

Cage Type	Ganged
Thermal Accessory Type Included	Heat Sink
Form Factor	QSFP+
Pluggable I/O Product Type	Cage Assembly
Sealable	Yes

Electrical Characteristics

Data Rate (Max)	14 Gb/s
-----------------	---------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Other

Included Lightpipe	No
EMI Containment Feature Type	Elastomeric Gasket
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold:



Octamethylcyclotetrasiloxane (D4) (.2% in Component)

Article Safe Usage Statements:
Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---


Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2215057-1 ASSY, SEATING TL, QSFP 1X4	TE Part # 2829040-4 QSFP IB EDR, 30AWG, 1.0M	TE Part # 2821033-8 QSFP TO [4]SFP+, 28G, 1M, 33AWG	TE Part # 2110819-1 QSFP+ Enh EVERCLEAR PT Conn
TE Part # 2202165-5 QSFP TO QSFP, 26AWG, FDR, 5.0 METER	TE Part # 2202165-4 QSFP TO QSFP, 26AWG, FDR, 4.0 METER	TE Part # 2829040-7 QSFP IB EDR, 26AWG, 2.0M	TE Part # 2829040-8 QSFP IB EDR, 26AWG, 3.0M



TE Part # 1888810-2
EMI/Dust Cover,XFP And QSFP



TE Part # 2053453-5
C/A, QSFP TO 4XSFP+, 4.0M



TE Part # 2829040-2
QSFP IB EDR, 33AWG, 1.0M



TE Part # CAT-C11-H5011142
QSFP to QSFP I/O Cable Assembly: 33 AWG



TE Part # 1-2053638-6
C/A, QSFP, 0.5M, P1-P2, UNEQUALIZED



TE Part # 2829040-6
QSFP IB EDR, 30AWG, 2.0M



TE Part # CAT-C11-H50111
QSFP-Four SFP+ I/O Cable Assembly 30 AWG


Also in the Series | **QSFP/QSFP+**




Light Pipes(8)



Pluggable I/O Cable Assemblies(13)



Pluggable IO Connectors & Cages(154)



QSFP, QSFP+ & zQSFP+(154)


Customers Also Bought



TE Part #487526-4
005 HOUSING FFC RCPT 100CL SR



TE Part #640457-3
03P MTA100 HDR ASSY SQ R/A F/L




TE Part #5103310-1
A/L LOW PRO HDR 10P RA BLACK




TE Part #5103309-1
A/L LOW PRO HDR 10P VERT BLACK



TE Part #60620-1
CMNL PIN 20-14 TPBR L/P




TE Part #1-480426-0
04P CMNL CAP HSG F/H NATL



TE Part #1888810-2
EMI/Dust Cover,XFP And QSFP



TE Part #2110819-1
QSFP+ Enh EVERCLEAR PT Conn



TE Part #103906-4
05 MTE HDR SRRA LATCH .100CL



TE Part #1473150-4
SEMI-HARD TRAY ASSY DDR2
SODIMM 5.2H RV

Documents

Product Drawings

1X4 CAGE ASSEMBLY, THRU BEZEL, W/ GASKET

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2170287-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2170287-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2170287-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English