




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **3000 – 4919 CMA**

Mating Tab Width: **6.35 mm [.25 in]**

Features

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Dimensions

Compatible Insulation Diameter Range	4.83 mm[.19 in]
Wire Size	3000 – 4919 CMA

Product Type Features

Insertion Force	Normal
-----------------	--------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	Compression Crimp
Barrel Type	Closed



Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Packaging Features

Packaging Method	Loose Piece
------------------	-------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-165536-2
PIDG BLUE POSI-LOK250X032,TAPE



TE Part # 2392022-1
BLUE BATTERY DAHT KIT 110V (47387-7)



TE Part # 169404
CERTI-LOK DIE




TE Part # 2323802-2
SSRMP-240D16 = Mini Puck,16A,240V AC



TE Part # 47387-7
DAHT PG PIDG 16-12 ASSY



TE Part # 2323802-8
SSRMP-240D16R = Mini Puck,16A, 240V AC,R



TE Part # 2392022-2
BLUE BATTERY DAHT KIT 220V (47387-7)



TE Part # 1-2323802-2
SSRMP-480D16R = Mini Puck,16A, 480V AC,R




TE Part # 169400
CERTI-LOK FRAME W/O DIES



TE Part # 2-1377175-6
SMP 0-0165536-1

Customers Also Bought



TE Part #216000-2
6P. TOOLLESS MOD J.



TE Part #5787956-1
SOCKET ASSY IEEE1394



TE Part #9-1768016-7
CSL-14033P-9



TE Part #1-2372389-0
MICRO MNL, HDR ASSY, SINGLE ROW, AU




TE Part #214011-E
SRCA 1,27 2 M 1 SMD 137 E1 094 * GURT *



TE Part #364485-E
SRCP 1,27 4 F 1 SMD 137 * 094 * GURT RLV



TE Part #384845-E
SRCP 1,27 2 F 1 SMD 137 * 094 * GURT RLV



TE Part #282045-015
44A0111-24-5



Documents

Product Drawings

PIDG POS.LOCK ASSY

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_165536-1_E2.2d_dxf.zip

English

Customer View Model

ENG_CVM_165536-1_E2.3d_igs.zip

English

Customer View Model

ENG_CVM_165536-1_E2.3d_stp.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_165536-1_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_165536-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_165536-1_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

PIDG_FASTON

English

Ultra-Fast and Ultra Fast Plus

English

165536-1

Quick Disconnect Receptacle, 15.5 – 13.5 AWG, 1.5 – 2.5 mm² Wire, 3000 – 4919 CMA, 6.35 mm [.25 in] Tab Width, Straight, Brass, Tin Plating

