



Connectors > Terminal Blocks & Strips > Terminal Block & Strip Accessories > Terminal Block & Strip Marking Accessories



Marking Product Type: **Label Protection Cap**
Primary Product Color: **Clear**
Operating Temperature Range: **-55 – 110 °C [-67 – 230 °F]**
UL Flammability Rating: **UL 94V-0**
EU RoHS Compliance: **Compliant**

Features

Configuration Features

Number of Cards per Package	20
-----------------------------	----

Dimensions

Product Width	6 mm[.236 in]
Product Depth	2.4 mm
Product Length	2.4 mm[.094 in]
Product Height	12 mm[.472 in]

Usage Conditions

Installation Temperature Range	-5 – 40 °C[23 – 104 °F]
Operating Temperature Range	-55 – 110 °C[-67 – 230 °F]

Body Features

Product Weight	.8 g[.028 oz]
Primary Product Material	Polycarbonate
Primary Product Color	Clear

Product Type Features

Marking Product Type	Label Protection Cap
----------------------	----------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------



Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1SNK506067R0000
ZS6-3S-YL



TE Part # 1SNK706066R0000
ZK4-BK




TE Part # 1SNK506151R0000
ZS6-3S-PE



TE Part # 1SNK706152R0000
ZK4-PE-4P




TE Part # 1SNK506066R0000
[ZS6-BK](#)




TE Part # 1SNK708031R0000
[ZK6-3P-OR](#)




TE Part # 1SNK708062R0000
[ZK6-RD](#)




TE Part # 1SNK710010R0000
[ZK10](#)




TE Part # 1SNK506063R0000
[ZS6-PR](#)



TE Part # 1SNK706032R0000
[ZK4-4P-OR](#)




TE Part # 1SNK708020R0000
[ZK6-BL](#)




TE Part # 1SNK706412R0000
[ZK2.5-SF-R3](#)




TE Part # 1SNK712150R0000
[ZK16-PE](#)



TE Part # 1SNK506416R0000
[ZS4-SF-R4](#)



TE Part # 1SNK506022R0000
[ZS6-4S-BL](#)




TE Part # 1SNK506230R0000
[ZS6-D2-OR](#)




TE Part # 1SNK506152R0000
[ZS6-4S-PE](#)



TE Part # 1SNK706010R0000
[ZK4](#)




TE Part # 1SNK710030R0000
[ZK10-OR](#)



TE Part # 1SNK706031R0000
[ZK4-3P-OR](#)


Also in the Series | **ENTRELEC HTP600**



[Printer Accessories\(13\)](#)




[Printer Ribbons\(4\)](#)



[Printers\(1\)](#)



[Terminal Block & Strip Insulating Accessories\(3\)](#)



Terminal Block & Strip Marking Accessories(113)


Customers Also Bought



TE Part #CAT-104MTA-PVUNH
PCB Header: Polyester, Vertical, Unshrouded, No Mating Alignment




TE Part #640457-4
04P MTA100 HDR ASSY SQ R/A F/L



TE Part #3-640469-3
03P MTA100 CONN ASSY ON TAPE



TE Part #3-2176057-9
RLP73K 3A R39 1% 1K RL



TE Part #640643-2
02P MTA156 COVER F/T



TE Part #3-640602-2
02P MTA156 CONN ASSY 24AWG LF



TE Part #2-2176326-5
CRGP 0603 1K0 1%



TE Part #3-640477-2
02 CIR MTA156 ASSY ON TAPE LF



TE Part #1-5164711-6
16pos.MINI-MATCH FBTB, 2.5mm pitch

Documents

Product Drawings

PROCAP6

French

Datasheets & Catalog Pages

PROCAP6

English

ENTRELEC Terminal Blocks Catalogue (RUS)

1SNK900612R0000

Label Protection Cap, Clear, -55 – 110 °C [-67 – 230 °F], UL 94V-0, ENTRELEC HTP600,
Terminal Block & Strip Marking Accessories

