

Neohm | Neohm CPF

TE Internal #: 2176238-6

Surface Mount Precision Resistor, Thin Film, 0805, .1 W, 20 ohm, .1

%, ± 25 ppm/ $^{\circ}$ C, Solder, 2 Terminations, Height .55 mm [.022 in],

Neohm CPF

[View on TE.com >](#)

Passive Components > Resistors > Surface Mount Resistors

Resistor Type: **Precision Resistor**Element Type: **Thin Film**Package Size Code: **0805**Power Rating: **.1 W**Resistance Value: **20 Ω**

Features

Industry Standards

Moisture Sensitivity Level	1
----------------------------	---

Usage Conditions

Operating Temperature Range	-55 – 155 $^{\circ}$ C
-----------------------------	------------------------

Temperature Coefficient	± 25 ppm/ $^{\circ}$ C
-------------------------	----------------------------

Electrical Characteristics

Operating Voltage	100 V
-------------------	-------

Power Rating	.1 W
--------------	------

Resistance Value	20 Ω
------------------	-------------

Resistance Class	Up to 1k Ω
------------------	-------------------

Passive Component Tolerance	.1 %
-----------------------------	------

Product Type Features

Resistor Type	Precision Resistor
---------------	--------------------

Element Type	Thin Film
--------------	-----------

Package Size Code	0805
-------------------	------

Configuration Features

Number of Resistors	1
---------------------	---

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.55 mm [.022 in]
Product Length	2 mm [.079 in]
Product Width	1.25 mm [.049 in]

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits

as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



Also in the Series | Neohm CPF



Customers Also Bought



Documents

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2176238-6_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2176238-6_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2176238-6_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Automotive Grade Thin Film Chip Resistor - Type CPF-A Series](#)

English