




Connectors > Terminal Blocks & Strips > Terminal Block & Strip Accessories > Terminal Block & Strip Mounting & Retention Accessories



Mounting & Retention Accessory Type: **Coding Peg**

Product Length: **7.8 mm [.307 in]**

Operating Temperature Range: **-55 – 110 °C [-67 – 230 °F]**

EU RoHS Compliance: **Compliant**

EU ELV Compliance: **Compliant**

Features

Industry Standards

IP Rating	IP20
UL Flammability Rating	UL 94V-0

Usage Conditions

Installation Temperature Range	-5 – 40 °C[23 – 104 °F]
Operating Temperature Range	-55 – 110 °C[-67 – 230 °F]

Dimensions

Product Width	3.5 mm[.138 in]
Product Depth	7.8 mm[.307 in]
Product Height	2 mm[.078 in]
Product Length	7.8 mm[.307 in]

Body Features

Product Weight	4.57 g[.161 oz]
Primary Product Color	Dark Gray
Primary Product Material	Polyamide



Mounting & Retention Accessory Type

Coding Peg

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1SNK805020R0000
ZDK2.5-22-BL




TE Part # 1SNK805212R0000
ZDK2.5-D2-PE



TE Part # 1SNK805014R0000
ZDK2.5-21




TE Part # 1SNK805156R0000
ZD2.5-22-PE



TE Part # 1SNK805016R0000
[ZD2.5-11](#)




TE Part # 1SNK805010R0000
[ZDK2.5-22](#)



TE Part # 1SNK805152R0000
[ZDK2.5-22-PE](#)



TE Part # 1SNK806010R0000
[ZDK4-22](#)




TE Part # CAT-ABN-SPC300025
[ENTRELEC Dynamic Pluggable SNK Series](#)




TE Part # 1SNK805214R0000
[ZDK2.5-D1](#)




TE Part # 1SNK805013R0000
[ZDS4-22](#)



TE Part # 1SNK805213R0000
[ZDK2.5-D2](#)




TE Part # 1SNK805015R0000
[ZDK2.5-11](#)



TE Part # 1SNK805025R0000
[ZDK2.5-11-BL](#)




TE Part # 1SNK805150R0000
[ZDK2.5-11-PE](#)




TE Part # 1SNK805017R0000
[ZD2.5-22](#)



TE Part # 1SNK806013R0000
[ZDS4-22-R1](#)




TE Part # 1SNK805250R0000
[ZDK2.5-D1-PE](#)



TE Part # 1SNK805223R0000
[ZDK2.5-D2-BL](#)

Customers Also Bought



TE Part # 1SET411014R0000
[WD-1-DP-GR4060](#)



TE Part # 1SNK505212R0000
[ZS4-T3](#)



TE Part # 1SNK506010R0000
[ZS6](#)



TE Part # 1SNK805150R0000
[ZDK2.5-11-PE](#)



TE Part #1SNL317510R0000
DBL175



TE Part #1SNK505211R0000
ZS4-D1




TE Part #1SNK805014R0000
ZDK2.5-21



TE Part #1SNK805753R0000
CDK2.5-PE-E



TE Part #1SNK805914R0000
EDK2.5-21



TE Part #1SNA008289R1600
FU520

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1SNK900636R0000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1SNK900636R0000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1SNK900636R0000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

COP-ZD

English

SNK SERIES TERMINAL BLOCKS

English

ENTRELEC Terminal Blocks Catalogue (RUS)

ENTRELEC Terminal Block - Master Catalog

ENTRELEC Terminal Block - Master Catalog

English