




Connectors > Pluggable IO Connectors & Cages



Form Factor: **SFP+**

Pluggable I/O Product Type: **Cage Assembly**

Sealable: **No**

Circuit Application: **Signal**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
---------------------------	--------------------------

Body Features

Heat Sink Style	Pin
	.255 in
Heat Sink Height Class	Networking

Packaging Features

Packaging Method	Tray
------------------	------

Operation/Application

Pluggable I/O Applications	SFP+
Heat Sink Compatible	Yes
Circuit Application	Signal

Product Type Features

Cage Type	Single
Thermal Accessory Type Included	Heat Sink
Form Factor	SFP+



Pluggable I/O Product Type	Cage Assembly
Sealable	No

Configuration Features

Number of Ports	1
Port Matrix Configuration	1 x 1

Electrical Characteristics

Data Rate (Max)	16 Gb/s
-----------------	---------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Other

Included Lightpipe	No
EMI Containment Feature Type	Internal/External EMI Springs
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits




as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # CAT-C11-N490333
QSFP28-Four SFP+ Cable Assembly:
30 AWG




TE Part # CAT-Q17-N490333
QSFP56-Four SFP56 Cable Assembly:
26 AWG




TE Part # CAT-C11-N490325
QSFP28-Four SFP+ Cable Assembly:
26 AWG




TE Part # CAT-C11-N4901114
SFP28 to SFP28 Cable Assembly: 30
AWG




TE Part # 4-2821222-5
SFP56 DIRECT ATTACH CA, 2M,
30AWG




TE Part # 2215087-5
KIT, SEATING TOOL, 1X1 SFP+




TE Part # 4-2821224-5
SFP56 DIRECT ATTACH CA, 3M,
26AWG




TE Part # 2334985-2
SFP28 DIRECT ATTACH CA, 1M,
32AWG




TE Part # CAT-Q17-N49011
QSFP56-Four SFP56 Cable Assembly:
30 AWG




TE Part # CAT-C11-N49011
SFP28 to SFP28 Cable Assembly: 26
AWG



TE Part # 1-2215067-0
ASSY, EXTRACTION TOOL, SFP+



TE Part # 2821033-8
QSFP TO [4]SFP+, 28G, 1M, 33AWG



TE Part # 4-2334985-2
SFP56 DIRECT ATTACH CA, 1M,
32AWG

Customers Also Bought



TE Part #CAT-SF59-C117ST123
SFP+ Stacked Cage Assemblies

TE Part #5179031-5
0.8FH,P08H.5,120,08/Sn,TU

TE Part #2187194-1
SW PIR RECT, 100OHM, 9X6SP

TE Part #2334884-1
UMCC Micro-Coax receptacle, Gen 4

TE Part #1-2176380-6
RQ 0805 1K65 0.1% 10PPM 5K RL

TE Part #1-1571983-3
GDH10S04=DIP SWITCH

TE Part #38941-12L
CONT PIN

TE Part #254370-E
STVB/3 20 F AB VV 7-00 TL 4,0 * 247 E007

TE Part #384275-E
STVB/3 20 M AB VV 4-00 0606 * * 247 E007

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2291634-3_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2291634-3_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2291634-3_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English