

Passive Components > Resistors > Through-Hole Resistors

Resistor Type: **Power Resistor**Element Type: **Metal Film**Power Rating: **1 W**Resistance Class: **Up to 1k Ω** Resistance Value: **6.2 Ω**

Features

Electrical Characteristics

| | |
|-----------------------------|-------------------|
| Operating Voltage | 350 V |
| Power Rating | 1 W |
| Resistance Class | Up to 1k Ω |
| Resistance Value | 6.2 Ω |
| Passive Component Tolerance | 5 % |

Product Type Features

| | |
|---------------|----------------|
| Resistor Type | Power Resistor |
| Element Type | Metal Film |

Configuration Features

| | |
|---------------------|---|
| Number of Resistors | 1 |
|---------------------|---|

Body Features

| | |
|-----------|--------------|
| Lead Type | Axial-Leaded |
|-----------|--------------|

Termination Features

| | |
|--------------------------------|--------|
| Termination Area Base Material | Copper |
| Number of Terminations | 2 |

Dimensions

| | |
|------------------------------|--------------|
| Passive Component Dimensions | 6.8 x 2.6 mm |
|------------------------------|--------------|

Usage Conditions

| | |
|-------------------------|------------------|
| Temperature Coefficient | ± 300 ppm/°C |
|-------------------------|------------------|

Packaging Features

| | |
|------------------|-------------|
| Packaging Method | Ammo Packed |
|------------------|-------------|

Other

| | |
|--------------------|-----------|
| EU RoHS Compliance | Compliant |
|--------------------|-----------|

| | |
|-------------------|-----------|
| EU ELV Compliance | Compliant |
|-------------------|-----------|

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

| | |
|------------------------------|-----------|
| EU RoHS Directive 2011/65/EU | Compliant |
|------------------------------|-----------|

| | |
|-----------------------------|-----------|
| EU ELV Directive 2000/53/EC | Compliant |
|-----------------------------|-----------|

| | |
|---|---|
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
|---|---|

| | |
|--|---|
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUL 2021 (219) |
|--|---|

Does not contain REACH SVHC

| | |
|-----------------|---|
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
|-----------------|---|

| | |
|---------------------------|------------------------------|
| Solder Process Capability | Wave solder capable to 265°C |
|---------------------------|------------------------------|


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 5-1879352-5
RR02 5% 56R AMMOTE Part # 8-1879354-5
RR03 5% 1K0 AMMOTE Part # 4-1879350-9
RR01 5% 22R AMMOTE Part # 7-1879352-7
RR02 5% 470R AMMOTE Part # 6-1879354-6
RR03 5% 160R AMMO

Also in the Series | Neohm RR



Through-Hole Resistors(478)

Customers Also Bought

TE Part #2-1393223-5
V23061B1007A501=MINISTARKSTROM

Documents

CAD Files

[3D PDF](#)

3D

[Customer View Model](#)[ENG_CVM_CVM_3-1879350-6_BA.2d_dxf.zip](#)

English

Customer View Model[ENG_CVM_CVM_3-1879350-6_BA.3d_igs.zip](#)

English

Customer View Model[ENG_CVM_CVM_3-1879350-6_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.**Datasheets & Catalog Pages**[4-1773460-6_RESISTIVE_SOLUTIONS_RAIL](#)

English

[1309350_PASSIVE_COMPONENT](#)

English

[Power Resistor - Type RR Series - Tyco Electronics Passives](#)

English

[8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS](#)

English