



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**

Element Type: **Thin Film**

Package Size Code: **0402**

Power Rating: **.063 W**

Resistance Value: **93.1K Ω**

Features

Industry Standards

Moisture Sensitivity Level	1
----------------------------	---

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film
Package Size Code	0402

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Power Rating	.063 W
Resistance Value	93.1K Ω
Resistance Class	1k Ω – 1M Ω
Passive Component Tolerance	.1 %

Termination Features

--	--



Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.3 mm[.012 in]
Product Length	1 mm[.039 in]
Product Width	.5 mm[.02 in]

Usage Conditions

Temperature Coefficient	±25 ppm/°C
-------------------------	------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2176280-3
CPF 0402 102K 0.1% 25PPM 1K RL

TE Part # 5-1879212-7
CPF 0402 82K5 0.1% 25PPM 5K RL

Also in the Series | Neohm CPF

Surface Mount Resistors(5842)

Customers Also Bought

TE Part #5227222-6
VERT JK W/MTG PINS, BNC PCB

TE Part #1888247-1
20 POS SMT CONN, SFP/SFP+, 30A

TE Part #5650947-5
ASSY,PIN,EUROCARD,TYPE C,LEAD-

TE Part #5206478-5
CLAMSHELL SIZE 5 W/RETAINER

TE Part #1-2176323-3
SMV 2W 1M0 5%

TE Part #6-1879134-1
RN 0603 42K2 0.1% 10PPM 1K RL

TE Part #3-1393788-6
V23079B1203B301

TE Part #020318030006-M
HSIR-750-1000-006

Documents

Product Drawings
CPF 0402 93K1 0.1% 25PPM 5K RL

CPF0402B93K1E

Surface Mount Precision Resistor, Thin Film, 0402, .063 W, 93.1K ohm, .1 %, ±25 ppm/°C, Solder, 2 Terminations, Height .3 mm [.012 in], Neohm CPF



English

Datasheets & Catalog Pages

CPF-1016

English