

# UM-D37M/DS/FU/LED/DG/C300/R - Termination board



2905133

<https://www.phoenixcontact.com/us/products/2905133>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE module intended for use with Honeywell Experion C300 16-channel digital cards:



## Your advantages

- These VARIOFACE modules are used in combination with the relevant front adapters
- UM-PRO housing
- DIN rail mounting
- LED blown fusing indication
- Per channel disconnects with test points
- Per channel pluggable 1 A fusing
- Designed to be mounted on the right side of the cabinet

## Commercial data

Item number	2905133
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	CK218H
GTIN	4046356959049
Weight per piece (including packing)	373.3 g
Weight per piece (excluding packing)	99.99 g
Customs tariff number	85371098
Country of origin	US

## Technical data

### Product properties

Product type	Interface module
Product family	VARIOFACE
Number of positions	37
No. of channels	16

### Electrical properties

Nominal voltage $U_N$	24 V DC
Max. current carrying capacity per branch	1 A (fuse limited)

#### Supported controller HONEYWELL Experion PKS C300/C-Series

Suitable I/O card	TDIL01 (non-redundant)
	TDIL11 (redundant)
	TDIL51 (non-redundant)
	TDIL61 (redundant)
	TDOB01 (non-redundant)
	TDOB11 (redundant)
	TDOB51 (non-redundant)
	TDOB61 (redundant)

#### Supported controller HONEYWELL Experion LX Series 8

Suitable I/O card	8X-TDILA1
	8X-TDILB1

## Connection data

### Field level

Connection method	Screw connection with disconnect knife
Stripping length	8 mm
Screw thread	M 3
Conductor cross section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross section AWG	24 ... 12

### Controller level

Connection method	D-SUB pin strip
Number of connections	1
Number of positions	37

## Signaling

Status display	no
Status display present	Yes, if the fuse fails

## Dimensions

# UM-D37M/DS/FU/LED/DG/C300/R - Termination board



2905133

<https://www.phoenixcontact.com/us/products/2905133>

## Item dimensions

Width	124 mm
Height	142.3 mm
Depth	65.6 mm

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 75 °C

## Standards and regulations

Standards/regulations	DIN EN 50178
-----------------------	--------------

## Mounting


Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

## Notes


General	Standard or halogen-free cables
Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

## Drawings

Circuit diagram



Dimensional drawing



dimensional drawing of left hand version

# UM-D37M/DS/FU/LED/DG/C300/R - Termination board



2905133

<https://www.phoenixcontact.com/us/products/2905133>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2905133>



**cUL Recognized**  
Approval ID: E238705



**UL Recognized**  
Approval ID: E238705

**cULus Recognized**

# UM-D37M/DS/FU/LED/DG/C300/R - Termination board



2905133

<https://www.phoenixcontact.com/us/products/2905133>

## Classifications

### ECLASS

ECLASS-11.0	27141152
ECLASS-12.0	27141152
ECLASS-13.0	27141152

### ETIM

ETIM 9.0	EC002780
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	1871e580-4568-4af7-97ed-751b13add147